

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245722

Luminaire Tested: **LD8B40D010 ER8B40940 8LBM0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245722  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201629)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B40D010 ER8B40940 8LBM0GPH  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
90 CRI 4000 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3450.0 lumens  
Efficiency: N/A  
Efficacy: 84.4 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 40.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245722

CATALOG NUMBER: LD8B40D010 ER8B40940 8LBM0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P245722

CATALOG NUMBER: LD8B40D010 ER8B40940 8LBM0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86	90	87	84	88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66
7	84	75	69	65	82	74	68	64	73	68	64	72	67	64	70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	134946
5°	131521
10°	117930
15°	105011
20°	95814
25°	87013
30°	71359
35°	46987
40°	23416
45°	8709
50°	2648
55°	301
60°	179
65°	0
70°	126
75°	512
80°	0
85°	495



TEST NUMBER: P245722

CATALOG NUMBER: LD8B40D010 ER8B40940 8LBM0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	389.6	11.3
10°-20°	926.3	26.8
20°-30°	1153.8	33.4
30°-40°	778.6	22.6
40°-50°	184.0	5.3
50°-60°	13.4	0.4
60°-70°	2.3	0.1
70°-80°	1.7	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2469.7	71.6
0°-40°	3248.2	94.2
0°-60°	3445.6	99.9
0°-90°	3450.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3450.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4376	
5°	4249	390
15°	3289	926
25°	2557	1154
35°	1248	779
45°	200	184
55°	6	13
65°	0	2
75°	4	2
85°	1	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P245722

CATALOG NUMBER: LD8B40D010 ER8B40940 8LBM0GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4376.2
2.5°	4369.3
5°	4248.9
7.5°	4032.3
10°	3766.3
12.5°	3512.9
15°	3289.4
17.5°	3096.7
20°	2919.8
22.5°	2748.6
25°	2557.4
27.5°	2308.4
30°	2004.1
32.5°	1636.1
35°	1248.2
37.5°	893.2
40°	581.7
42.5°	348.1
45°	199.7
47.5°	111.9
50°	55.2
52.5°	25.5
55°	5.6
57.5°	1.4
60°	2.9
62.5°	4.3
65°	0.0
67.5°	2.9
70°	1.4
72.5°	1.4
75°	4.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	1.4
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P245722

CATALOG NUMBER: LD8B40D010 ER8B40940 8LBM0GPH

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)