

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250846

Luminaire Tested: **LD8B60D010 ER8B60840 8LBMOLI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250846  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-11)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B60D010 ER8B60840 8LBM0LI  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 4000 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6428.0 lumens  
Efficiency: N/A  
Efficacy: 108.0 lumens/watt  
Spacing Criteria (0/90/45): 0.63 / 0.63 / 0.72  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250846

CATALOG NUMBER: LD8B60D010 ER8B60840 8LBM0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P250846

CATALOG NUMBER: LD8B60D010 ER8B60840 8LBM0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	73	80	75	72		79	75	72		77	74	71	70
7	86	78	72	69	85	77	72	68	76	71	68		75	71	68		74	70	67	66
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	60	59
10	76	67	62	58	75	67	61	58	66	61	58		65	61	58		64	60	58	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	345783
5°	330921
10°	294605
15°	236673
20°	185367
25°	149669
30°	115975
35°	66054
40°	24917
45°	10745
50°	4322
55°	1613
60°	863
65°	584
70°	361
75°	238
80°	0
85°	0



TEST NUMBER: P250846

CATALOG NUMBER: LD8B60D010 ER8B60840 8LBM0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	981.2	15.3
10°-20°	2058.7	32.0
20°-30°	2014.5	31.3
30°-40°	1114.5	17.3
40°-50°	215.7	3.4
50°-60°	33.1	0.5
60°-70°	8.1	0.1
70°-80°	2.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5054.4	78.6
0°-40°	6168.9	96.0
0°-60°	6417.7	99.8
0°-90°	6428.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6428.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11214	
5°	10691	981
15°	7414	2059
25°	4399	2014
35°	1755	1115
45°	246	216
55°	30	33
65°	8	8
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P250846

CATALOG NUMBER: LD8B60D010 ER8B60840 8LBM0LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	11213.5
2.5°	11059.3
5°	10690.7
7.5°	10173.9
10°	9408.7
12.5°	8441.2
15°	7413.6
17.5°	6450.1
20°	5648.8
22.5°	4985.8
25°	4398.9
27.5°	3846.0
30°	3257.1
32.5°	2566.0
35°	1754.7
37.5°	1055.7
40°	619.0
42.5°	386.6
45°	246.4
47.5°	154.2
50°	90.1
52.5°	50.1
55°	30.0
57.5°	18.0
60°	14.0
62.5°	10.0
65°	8.0
67.5°	6.0
70°	4.0
72.5°	2.0
75°	2.0
77.5°	2.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)