

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251062

Luminaire Tested: **LD8B60D010 ER8B60840 8LBM0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251062
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201704)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B60840 8LBM0WMH
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
80 CRI 4000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5926.0 lumens
Efficiency: N/A
Efficacy: 99.6 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.83
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251062

CATALOG NUMBER: LD8B60D010 ER8B60840 8LBM0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P251062

CATALOG NUMBER: LD8B60D010 ER8B60840 8LBM0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74	81	77	73	79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	229394
5°	233799
10°	222913
15°	196831
20°	170571
25°	144126
30°	108312
35°	72522
40°	40612
45°	16314
50°	5651
55°	1564
60°	888
65°	773
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P251062

CATALOG NUMBER: LD8B60D010 ER8B60840 8LBM0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	706.7	11.9
10°-20°	1719.7	29.0
20°-30°	1908.4	32.2
30°-40°	1209.0	20.4
40°-50°	335.4	5.7
50°-60°	38.4	0.6
60°-70°	7.6	0.1
70°-80°	0.8	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4334.8	73.1
0°-40°	5543.8	93.6
0°-60°	5917.7	99.9
0°-90°	5926.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5926.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7439	
5°	7553	707
15°	6166	1720
25°	4236	1908
35°	1926	1209
45°	374	335
55°	29	38
65°	11	8
75°	0	1
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251062

CATALOG NUMBER: LD8B60D010 ER8B60840 8LBM0WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	7439.1
2.5°	7494.2
5°	7553.1
7.5°	7435.4
10°	7119.1
12.5°	6668.0
15°	6165.6
17.5°	5672.2
20°	5197.9
22.5°	4732.5
25°	4236.0
27.5°	3655.5
30°	3041.9
32.5°	2447.5
35°	1926.5
37.5°	1455.8
40°	1008.9
42.5°	627.4
45°	374.1
47.5°	215.1
50°	117.8
52.5°	57.7
55°	29.1
57.5°	21.9
60°	14.4
62.5°	7.6
65°	10.6
67.5°	5.3
70°	0.0
72.5°	1.5
75°	0.0
77.5°	1.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251062

CATALOG NUMBER: LD8B60D010 ER8B60840 8LBM0WMH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)