

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250822

Luminaire Tested: **LD8B60D010 ER8B60840 8LBNOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250822
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-10)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B60840 8LBN0LI
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 4000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5907.0 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.32
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250822

CATALOG NUMBER: LD8B60D010 ER8B60840 8LBN0LI

Luminous Intensity Polar Plot





TEST NUMBER: P250822

CATALOG NUMBER: LD8B60D010 ER8B60840 8LBN0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	100	108	104	101	99	101	99	96	98	96	94	95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	91	94	92	89	92	90	88	87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83
5	98	91	86	83	96	90	86	82	88	85	82	87	84	81	85	83	80	79
6	94	87	82	79	93	86	82	78	85	81	78	83	80	77	82	79	77	76
7	91	83	78	75	90	83	78	75	81	77	74	80	77	74	79	76	74	72
8	88	80	75	72	86	79	75	71	78	74	71	77	74	71	76	73	71	70
9	85	77	72	69	84	76	72	69	75	71	68	75	71	68	74	70	68	67
10	82	74	69	66	81	73	69	66	73	69	66	72	68	66	71	68	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	892415
5°	619828
10°	326168
15°	206370
20°	153362
25°	120571
30°	86806
35°	37253
40°	12982
45°	4980
50°	1151
55°	430
60°	0
65°	584
70°	180
75°	477
80°	710
85°	0



TEST NUMBER: P250822

CATALOG NUMBER: LD8B60D010 ER8B60840 8LBN0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1605.3	27.2
10°-20°	1865.2	31.6
20°-30°	1609.8	27.3
30°-40°	698.4	11.8
40°-50°	109.4	1.9
50°-60°	7.9	0.1
60°-70°	4.2	0.1
70°-80°	4.5	0.1
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5080.3	86.0
0°-40°	5778.7	97.8
0°-60°	5896.1	99.8
0°-90°	5907.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5907.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	28940	
5°	20024	###
15°	6464	1865
25°	3544	1610
35°	990	698
45°	114	109
55°	8	8
65°	8	4
75°	4	4
85°	0	2
90°	0	



TEST NUMBER: P250822

CATALOG NUMBER: LD8B60D010 ER8B60840 8LBN0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	28940.4
2.5°	26133.9
5°	20024.1
7.5°	14280.9
10°	10416.7
12.5°	7992.8
15°	6464.4
17.5°	5436.7
20°	4673.5
22.5°	4022.4
25°	3543.7
27.5°	3038.9
30°	2437.9
32.5°	1694.7
35°	989.6
37.5°	552.9
40°	322.5
42.5°	200.3
45°	114.2
47.5°	92.1
50°	24.0
52.5°	12.0
55°	8.0
57.5°	4.0
60°	0.0
62.5°	2.0
65°	8.0
67.5°	6.0
70°	2.0
72.5°	10.0
75°	4.0
77.5°	0.0
80°	4.0
82.5°	2.0
85°	0.0
87.5°	4.0
90°	0.0

(END OF REPORT)