

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251086

Luminaire Tested: **LD8B60D010 ER8B60840 8LBS0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251086
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B60840 8LBS0WMH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 4000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6660.0 lumens
Efficiency: N/A
Efficacy: 111.9 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251086

CATALOG NUMBER: LD8B60D010 ER8B60840 8LBS0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P251086

CATALOG NUMBER: LD8B60D010 ER8B60840 8LBS0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55	64	58	54	63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	116441
5°	116081
10°	115040
15°	113899
20°	112675
25°	110895
30°	107849
35°	102934
40°	95394
45°	80546
50°	55260
55°	30477
60°	15319
65°	8624
70°	4697
75°	3336
80°	2131
85°	1415



TEST NUMBER: P251086

CATALOG NUMBER: LD8B60D010 ER8B60840 8LBS0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	355.5	5.3
10°-20°	1006.2	15.1
20°-30°	1498.1	22.5
30°-40°	1701.7	25.6
40°-50°	1391.0	20.9
50°-60°	545.1	8.2
60°-70°	127.0	1.9
70°-80°	30.6	0.5
80°-90°	4.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2859.7	42.9
0°-40°	4561.4	68.5
0°-60°	6497.5	97.6
0°-90°	6660.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6660.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3776	
5°	3750	355
15°	3568	1006
25°	3259	1498
35°	2734	1702
45°	1847	1391
55°	567	545
65°	118	127
75°	28	31
85°	4	5
90°	0	



TEST NUMBER: P251086

CATALOG NUMBER: LD8B60D010 ER8B60840 8LBS0WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3776.1
2.5°	3770.1
5°	3750.1
7.5°	3716.0
10°	3674.0
12.5°	3621.9
15°	3567.8
17.5°	3503.7
20°	3433.6
22.5°	3351.4
25°	3259.3
27.5°	3151.1
30°	3028.9
32.5°	2890.7
35°	2734.4
37.5°	2562.2
40°	2369.8
42.5°	2137.5
45°	1847.0
47.5°	1506.4
50°	1151.9
52.5°	827.3
55°	566.9
57.5°	370.6
60°	248.4
62.5°	170.3
65°	118.2
67.5°	78.1
70°	52.1
72.5°	36.1
75°	28.0
77.5°	20.0
80°	12.0
82.5°	6.0
85°	4.0
87.5°	2.0
90°	0.0

(END OF REPORT)