

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251194

Luminaire Tested: **LD8B60D010 ER8B60927 8LBS0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251194
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B60927 8LBS0WH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5456.3 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251194

CATALOG NUMBER: LD8B60D010 ER8B60927 8LBS0WH

Luminous Intensity Polar Plot





TEST NUMBER: P251194

CATALOG NUMBER: LD8B60D010 ER8B60927 8LBS0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70		77	73	69		75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57		66	60	56		64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51		61	55	51		60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47		56	51	47		55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43		52	47	43		51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39		49	43	39		48	43	39	38

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P251194

CATALOG NUMBER: LD8B60D010 ER8B60927 8LBS0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.1	5.4
10°-20°	874.3	16.0
20°-30°	1353.6	24.8
30°-40°	1466.4	26.9
40°-50°	1055.2	19.3
50°-60°	353.0	6.5
60°-70°	53.4	1.0
70°-80°	4.6	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2523.0	46.2
0°-40°	3989.4	73.1
0°-60°	5397.7	98.9
0°-90°	5456.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5456.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3090	
5°	3090	295
15°	3094	874
25°	2956	1354
35°	2364	1466
45°	1390	1055
55°	357	353
65°	47	53
75°	3	5
85°	0	1
90°	0	



TEST NUMBER: P251194

CATALOG NUMBER: LD8B60D010 ER8B60927 8LBS0WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3090.5
2.5°	3090.5
5°	3090.5
7.5°	3092.1
10°	3093.6
12.5°	3096.8
15°	3093.6
17.5°	3081.0
20°	3052.6
22.5°	3009.9
25°	2956.3
27.5°	2871.0
30°	2738.4
32.5°	2564.7
35°	2364.1
37.5°	2147.7
40°	1912.4
42.5°	1659.7
45°	1389.7
47.5°	1097.6
50°	814.8
52.5°	559.0
55°	356.8
57.5°	213.2
60°	127.9
62.5°	77.4
65°	47.4
67.5°	23.7
70°	11.0
72.5°	4.7
75°	3.2
77.5°	3.2
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)