

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245374

Luminaire Tested: **LD8B40D010 ER8B409727 8LBS0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245374
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B40D010 ER8B409727 8LBS0WH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3422.0 lumens
Efficiency: N/A
Efficacy: 83.7 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 40.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245374

CATALOG NUMBER: LD8B40D010 ER8B409727 8LBS0WH

Luminous Intensity Polar Plot





TEST NUMBER: P245374

CATALOG NUMBER: LD8B40D010 ER8B409727 8LBS0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70		77	73	69		75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57		66	60	56		64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51		61	55	51		60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47		56	51	47		55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43		52	47	43		51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39		49	43	39		48	43	39	38

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P245374

CATALOG NUMBER: LD8B40D010 ER8B409727 8LBS0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.1	5.4
10°-20°	548.3	16.0
20°-30°	848.9	24.8
30°-40°	919.7	26.9
40°-50°	661.8	19.3
50°-60°	221.4	6.5
60°-70°	33.5	1.0
70°-80°	2.9	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1582.4	46.2
0°-40°	2502.1	73.1
0°-60°	3385.3	98.9
0°-90°	3422.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3422.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1938	
5°	1938	185
15°	1940	548
25°	1854	849
35°	1483	920
45°	872	662
55°	224	221
65°	30	33
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P245374

CATALOG NUMBER: LD8B40D010 ER8B409727 8LBS0WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1938.3
2.5°	1938.3
5°	1938.3
7.5°	1939.3
10°	1940.2
12.5°	1942.2
15°	1940.2
17.5°	1932.3
20°	1914.5
22.5°	1887.8
25°	1854.1
27.5°	1800.6
30°	1717.4
32.5°	1608.5
35°	1482.7
37.5°	1347.0
40°	1199.4
42.5°	1040.9
45°	871.6
47.5°	688.3
50°	511.1
52.5°	350.6
55°	223.8
57.5°	133.7
60°	80.2
62.5°	48.5
65°	29.7
67.5°	14.9
70°	6.9
72.5°	3.0
75°	2.0
77.5°	2.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)