

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251348

Luminaire Tested: **LD8B60D010 ER8B60927 8LBW0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251348  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-47)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B60D010 ER8B60927 8LBW0B  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 2700 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3109.5 lumens  
Efficiency: N/A  
Efficacy: 52.3 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.02  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251348

CATALOG NUMBER: LD8B60D010 ER8B60927 8LBW0B

### Luminous Intensity Polar Plot





TEST NUMBER: P251348

CATALOG NUMBER: LD8B60D010 ER8B60927 8LBW0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	106	111	108	106	104	104	102	101		101	99	98		97	96	95	93
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92	90	88	86
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86	84	81	80
4	96	88	83	78	94	87	82	78	85	80	77		83	79	76		81	78	75	74
5	91	82	76	72	89	81	76	71	80	75	71		78	74	70		76	73	70	68
6	86	77	71	66	85	76	70	66	74	69	65		73	68	65		72	68	65	63
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67	63	60	58
8	77	67	61	57	76	67	61	57	66	60	56		65	60	56		64	59	56	54
9	73	63	57	53	72	63	57	53	62	56	52		61	56	52		60	55	52	51
10	70	59	53	49	68	59	53	49	58	53	49		57	52	49		57	52	49	47

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P251348

CATALOG NUMBER: LD8B60D010 ER8B60927 8LBW0B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	260.3	8.4
10°-20°	719.8	23.1
20°-30°	1027.7	33.1
30°-40°	851.7	27.4
40°-50°	210.0	6.8
50°-60°	37.8	1.2
60°-70°	2.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2007.8	64.6
0°-40°	2859.6	92.0
0°-60°	3107.3	99.9
0°-90°	3109.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3109.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2844	
5°	2761	260
15°	2558	720
25°	2255	1028
35°	1434	852
45°	224	210
55°	36	38
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P251348

CATALOG NUMBER: LD8B60D010 ER8B60927 8LBW0B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2843.5
2.5°	2819.8
5°	2761.4
7.5°	2704.6
10°	2657.1
12.5°	2611.4
15°	2557.7
17.5°	2494.6
20°	2423.5
22.5°	2343.0
25°	2254.6
27.5°	2134.6
30°	1976.7
32.5°	1754.1
35°	1433.6
37.5°	1035.7
40°	637.9
42.5°	371.0
45°	224.2
47.5°	148.4
50°	99.4
52.5°	64.7
55°	36.3
57.5°	17.3
60°	7.9
62.5°	3.2
65°	1.6
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)