

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250812

Luminaire Tested: **LD8B60D010 ER8B60927 8LBW0LI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250812  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B60D010 ER8B60927 8LBW0LI  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 2700 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5154.8 lumens  
Efficiency: N/A  
Efficacy: 86.6 lumens/watt  
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250812

CATALOG NUMBER: LD8B60D010 ER8B60927 8LBW0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P250812

CATALOG NUMBER: LD8B60D010 ER8B60927 8LBW0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55	54
8	74	63	56	52	72	62	56	52	61	55	51		60	55	51		59	54	51	49
9	70	59	52	48	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52	47	43	42

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P250812

CATALOG NUMBER: LD8B60D010 ER8B60927 8LBW0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	297.4	5.8
10°-20°	985.4	19.1
20°-30°	1550.4	30.1
30°-40°	1474.8	28.6
40°-50°	679.9	13.2
50°-60°	154.5	3.0
60°-70°	10.2	0.2
70°-80°	2.1	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2833.2	55.0
0°-40°	4308.0	83.6
0°-60°	5142.3	99.8
0°-90°	5154.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5154.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2966	
5°	3042	297
15°	3496	985
25°	3400	1550
35°	2417	1475
45°	832	680
55°	150	154
65°	7	10
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P250812

CATALOG NUMBER: LD8B60D010 ER8B60927 8LBW0LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2965.8
1°	2964.5
2°	2970.1
3°	2987.0
4°	3012.4
5°	3042.0
6°	3078.7
7°	3118.2
8°	3159.1
9°	3207.0
10°	3257.8
11°	3308.6
12°	3362.2
13°	3412.9
14°	3459.5
15°	3496.2
16°	3522.9
17°	3541.3
18°	3549.7
19°	3548.4
20°	3538.5
21°	3521.6
22°	3500.4
23°	3472.2
24°	3439.8
25°	3400.3
26°	3353.7
27°	3294.4
28°	3224.0
29°	3142.1
30°	3047.6
32.5°	2764.2
35°	2417.3
37.5°	2014.0
40°	1573.9
42.5°	1163.5
45°	832.0
47.5°	589.5
50°	406.1
52.5°	259.5
55°	149.5
57.5°	74.7
60°	32.4
62.5°	12.7
65°	7.1



TEST NUMBER: P250812

CATALOG NUMBER: LD8B60D010 ER8B60927 8LBW0LI

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	4.3
70°	2.8
72.5°	2.8
75°	1.5
77.5°	1.5
80°	1.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)