

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246611

Luminaire Tested: **LD8B50D010 ER8B50827 8LBN0MW**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246611  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201839)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B50D010 ER8B50827 8LBN0MW  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 2700 CCT WITH MATTE WHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4756.0 lumens  
Efficiency: N/A  
Efficacy: 89.7 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.85  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 53  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P246611

CATALOG NUMBER: LD8B50D010 ER8B50827 8LBN0MW

### Luminous Intensity Polar Plot





TEST NUMBER: P246611

CATALOG NUMBER: LD8B50D010 ER8B50827 8LBN0MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67
5	87	78	71	66	85	77	70	65	75	69	65	73	68	64	71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60	68	63	59	67	62	59	57
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	153799
5°	152697
10°	139147
15°	119268
20°	105701
25°	94325
30°	76177
35°	52852
40°	33536
45°	24910
50°	21262
55°	18639
60°	16682
65°	14907
70°	12848
75°	11819
80°	11010
85°	9730



TEST NUMBER: P246611

CATALOG NUMBER: LD8B50D010 ER8B50827 8LBN0MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	455.0	9.6
10°-20°	1052.4	22.1
20°-30°	1251.5	26.3
30°-40°	884.7	18.6
40°-50°	456.7	9.6
50°-60°	313.1	6.6
60°-70°	203.3	4.3
70°-80°	106.6	2.2
80°-90°	32.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2758.9	58.0
0°-40°	3643.6	76.6
0°-60°	4413.4	92.8
0°-90°	4756.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4756.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4988	
5°	4933	455
15°	3736	1052
25°	2772	1252
35°	1404	885
45°	571	457
55°	347	313
65°	204	203
75°	99	107
85°	28	31
90°	0	2
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P246611

CATALOG NUMBER: LD8B50D010 ER8B50827 8LBN0MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4987.6
2.5°	4987.6
5°	4933.0
7.5°	4751.6
10°	4443.9
12.5°	4077.0
15°	3736.0
17.5°	3455.5
20°	3221.1
22.5°	2999.4
25°	2772.3
27.5°	2487.2
30°	2139.4
32.5°	1765.2
35°	1404.0
37.5°	1081.8
40°	833.1
42.5°	670.4
45°	571.2
47.5°	499.2
50°	443.2
52.5°	394.1
55°	346.7
57.5°	305.0
60°	270.5
62.5°	234.4
65°	204.3
67.5°	177.0
70°	142.5
72.5°	122.4
75°	99.2
77.5°	80.5
80°	62.0
82.5°	46.1
85°	27.5
87.5°	15.8
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P246611

CATALOG NUMBER: LD8B50D010 ER8B50827 8LBN0MW

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)