

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251406

Luminaire Tested: **LD8B60D010 ER8B60930 8LBS0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251406  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-17)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B60D010 ER8B60930 8LBS0B  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
90 CRI 3000 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5264.2 lumens  
Efficiency: N/A  
Efficacy: 88.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.25  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251406

CATALOG NUMBER: LD8B60D010 ER8B60930 8LBS0B

### Luminous Intensity Polar Plot





TEST NUMBER: P251406

CATALOG NUMBER: LD8B60D010 ER8B60930 8LBS0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	99	94	90	103	98	93	89	94	90	87		91	88	85		88	86	84	82
3	98	90	84	79	96	89	83	79	86	81	77		84	80	76		81	78	75	73
4	92	82	76	70	90	81	75	70	79	73	69		77	72	68		75	71	67	66
5	86	75	68	63	84	74	68	63	72	66	62		71	65	61		69	64	61	59
6	80	69	62	56	78	68	61	56	67	60	56		65	60	55		64	59	55	53
7	75	63	56	51	73	63	56	51	61	55	51		60	54	50		59	54	50	48
8	70	59	51	46	69	58	51	46	57	50	46		56	50	46		54	49	46	44
9	66	54	47	42	65	54	47	42	53	46	42		52	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	39		48	42	38		47	42	38	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	94038
5°	93936
10°	93441
15°	92762
20°	91735
25°	90286
30°	87639
35°	83517
40°	77352
45°	64908
50°	42916
55°	21182
60°	8406
65°	3269
70°	505
75°	0
80°	0
85°	0



TEST NUMBER: P251406

CATALOG NUMBER: LD8B60D010 ER8B60930 8LBS0B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	288.0	5.5
10°-20°	819.1	15.6
20°-30°	1219.1	23.2
30°-40°	1380.8	26.2
40°-50°	1116.4	21.2
50°-60°	387.2	7.4
60°-70°	52.9	1.0
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2326.2	44.2
0°-40°	3707.0	70.4
0°-60°	5210.5	99.0
0°-90°	5264.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5264.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3050	
5°	3035	288
15°	2906	819
25°	2654	1219
35°	2219	1381
45°	1488	1116
55°	394	387
65°	45	53
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P251406

CATALOG NUMBER: LD8B60D010 ER8B60930 8LBS0B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3049.6
2.5°	3045.8
5°	3034.7
7.5°	3012.2
10°	2984.2
12.5°	2946.9
15°	2905.7
17.5°	2853.5
20°	2795.5
22.5°	2728.4
25°	2653.6
27.5°	2564.1
30°	2461.3
32.5°	2345.5
35°	2218.6
37.5°	2078.4
40°	1921.6
42.5°	1729.3
45°	1488.4
47.5°	1197.0
50°	894.6
52.5°	612.5
55°	394.0
57.5°	233.4
60°	136.3
62.5°	80.3
65°	44.8
67.5°	20.5
70°	5.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)