

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250814

Luminaire Tested: **LD8B60D010 ER8B60930 8LBW0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250814
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B60930 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5434.6 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250814

CATALOG NUMBER: LD8B60D010 ER8B60930 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P250814

CATALOG NUMBER: LD8B60D010 ER8B60930 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55	54
8	74	63	56	52	72	62	56	52	61	55	51		60	55	51		59	54	51	49
9	70	59	52	48	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52	47	43	42

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250814

CATALOG NUMBER: LD8B60D010 ER8B60930 8LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	313.5	5.8
10°-20°	1038.9	19.1
20°-30°	1634.6	30.1
30°-40°	1554.9	28.6
40°-50°	716.8	13.2
50°-60°	162.9	3.0
60°-70°	10.7	0.2
70°-80°	2.2	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2987.0	55.0
0°-40°	4541.8	83.6
0°-60°	5421.5	99.8
0°-90°	5434.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5434.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3127	
5°	3207	314
15°	3686	1039
25°	3585	1635
35°	2548	1555
45°	877	717
55°	158	163
65°	7	11
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P250814

CATALOG NUMBER: LD8B60D010 ER8B60930 8LBW0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3126.9
1°	3125.5
2°	3131.4
3°	3149.2
4°	3176.0
5°	3207.2
6°	3245.9
7°	3287.4
8°	3330.6
9°	3381.2
10°	3434.6
11°	3488.2
12°	3544.7
13°	3598.3
14°	3647.3
15°	3686.0
16°	3714.2
17°	3733.6
18°	3742.5
19°	3741.0
20°	3730.6
21°	3712.8
22°	3690.4
23°	3660.7
24°	3626.5
25°	3584.8
26°	3535.7
27°	3473.3
28°	3399.0
29°	3312.8
30°	3213.1
32.5°	2914.3
35°	2548.5
37.5°	2123.3
40°	1659.3
42.5°	1226.7
45°	877.3
47.5°	621.5
50°	428.2
52.5°	273.6
55°	157.6
57.5°	78.8
60°	34.2
62.5°	13.3
65°	7.4



TEST NUMBER: P250814

CATALOG NUMBER: LD8B60D010 ER8B60930 8LBW0LI

CANDELA DISTRIBUTION (continued):

	0°
67.5°	4.5
70°	3.0
72.5°	3.0
75°	1.5
77.5°	1.5
80°	1.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)