

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251452

Luminaire Tested: **LD8B60D010 ER8B60935 8LBN0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251452
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201839)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B60935 8LBN0MW
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 3500 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4898.0 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.85
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251452

CATALOG NUMBER: LD8B60D010 ER8B60935 8LBN0MW

Luminous Intensity Polar Plot





TEST NUMBER: P251452

CATALOG NUMBER: LD8B60D010 ER8B60935 8LBN0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67
5	87	78	71	66	85	77	70	65	75	69	65	73	68	64	71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60	68	63	59	67	62	59	57
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	158391
5°	157253
10°	143303
15°	122831
20°	108858
25°	97139
30°	78449
35°	54430
40°	34538
45°	25655
50°	21895
55°	19198
60°	17182
65°	15352
70°	13226
75°	12164
80°	11330
85°	10013



TEST NUMBER: P251452

CATALOG NUMBER: LD8B60D010 ER8B60935 8LBN0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	468.6	9.6
10°-20°	1083.8	22.1
20°-30°	1288.9	26.3
30°-40°	911.1	18.6
40°-50°	470.3	9.6
50°-60°	322.5	6.6
60°-70°	209.3	4.3
70°-80°	109.8	2.2
80°-90°	33.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2841.3	58.0
0°-40°	3752.4	76.6
0°-60°	4545.2	92.8
0°-90°	4898.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4898.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5136	
5°	5080	469
15°	3848	1084
25°	2855	1289
35°	1446	911
45°	588	470
55°	357	322
65°	210	209
75°	102	110
85°	28	32
90°	0	2
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251452

CATALOG NUMBER: LD8B60D010 ER8B60935 8LBN0MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5136.5
2.5°	5136.5
5°	5080.2
7.5°	4893.5
10°	4576.6
12.5°	4198.7
15°	3847.6
17.5°	3558.7
20°	3317.3
22.5°	3089.0
25°	2855.0
27.5°	2561.4
30°	2203.2
32.5°	1817.9
35°	1445.9
37.5°	1114.1
40°	858.0
42.5°	690.4
45°	588.3
47.5°	514.1
50°	456.4
52.5°	405.9
55°	357.1
57.5°	314.1
60°	278.6
62.5°	241.4
65°	210.4
67.5°	182.3
70°	146.7
72.5°	126.0
75°	102.1
77.5°	82.9
80°	63.8
82.5°	47.5
85°	28.3
87.5°	16.3
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251452

CATALOG NUMBER: LD8B60D010 ER8B60935 8LBN0MW

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)