

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251232

Luminaire Tested: **LD8B60D010 ER8B60935 8LBW0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251232
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B60935 8LBW0GPH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 3500 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4763.0 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251232

CATALOG NUMBER: LD8B60D010 ER8B60935 8LBW0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P251232

CATALOG NUMBER: LD8B60D010 ER8B60935 8LBW0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100		100	98	97		96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89		93	90	87		90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78	74	71	70
5	88	79	72	67	87	78	72	67	76	71	66		74	70	66		73	69	65	64
6	83	73	66	61	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		65	59	56		63	59	55	54
8	74	63	56	52	73	63	56	52	61	56	51		60	55	51		59	55	51	49
9	70	59	52	48	69	58	52	48	57	52	48		57	51	47		56	51	47	46
10	66	55	49	44	65	55	49	44	54	48	44		53	48	44		52	47	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	114363
5°	111661
10°	108158
15°	106595
20°	105340
25°	103079
30°	96548
35°	78834
40°	47065
45°	28267
50°	20374
55°	13865
60°	8696
65°	4268
70°	1082
75°	405
80°	302
85°	0



TEST NUMBER: P251232

CATALOG NUMBER: LD8B60D010 ER8B60935 8LBW0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	339.4	7.1
10°-20°	942.3	19.8
20°-30°	1383.8	29.1
30°-40°	1254.4	26.3
40°-50°	537.0	11.3
50°-60°	237.6	5.0
60°-70°	63.4	1.3
70°-80°	4.9	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2665.4	56.0
0°-40°	3919.9	82.3
0°-60°	4694.5	98.6
0°-90°	4763.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4763.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3709	
5°	3607	339
15°	3339	942
25°	3030	1384
35°	2094	1254
45°	648	537
55°	258	238
65°	58	63
75°	3	5
85°	0	0
90°	0	



TEST NUMBER: P251232

CATALOG NUMBER: LD8B60D010 ER8B60935 8LBW0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3708.7
2.5°	3679.5
5°	3607.3
7.5°	3524.7
10°	3454.2
12.5°	3395.8
15°	3339.0
17.5°	3278.9
20°	3210.1
22.5°	3129.3
25°	3029.6
27.5°	2895.4
30°	2711.5
32.5°	2453.6
35°	2094.2
37.5°	1623.1
40°	1169.2
42.5°	844.2
45°	648.2
47.5°	522.7
50°	424.7
52.5°	337.0
55°	257.9
57.5°	192.6
60°	141.0
62.5°	98.0
65°	58.5
67.5°	25.8
70°	12.0
72.5°	6.9
75°	3.4
77.5°	1.7
80°	1.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)