

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246479

Luminaire Tested: **LD8B50D010 ER8B50835 8LBS0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246479
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-17)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B50D010 ER8B50835 8LBS0B
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3500 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5017.0 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246479

CATALOG NUMBER: LD8B50D010 ER8B50835 8LBS0B

Luminous Intensity Polar Plot





TEST NUMBER: P246479

CATALOG NUMBER: LD8B50D010 ER8B50835 8LBS0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	99	94	90	103	98	93	89	94	90	87	91	88	85	88	86	84	82
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73
4	92	82	76	70	90	81	75	70	79	73	69	77	72	68	75	71	67	66
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59
6	80	69	62	56	78	68	61	56	67	60	56	65	60	55	64	59	55	53
7	75	63	56	51	73	63	56	51	61	55	51	60	54	50	59	54	50	48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44
9	66	54	47	42	65	54	47	42	53	46	42	52	46	42	51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	39	48	42	38	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	89620
5°	89522
10°	89051
15°	88407
20°	87430
25°	86047
30°	83523
35°	79591
40°	73721
45°	61860
50°	40897
55°	20187
60°	8011
65°	3116
70°	478
75°	0
80°	0
85°	0



TEST NUMBER: P246479

CATALOG NUMBER: LD8B50D010 ER8B50835 8LBS0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	274.5	5.5
10°-20°	780.6	15.6
20°-30°	1161.9	23.2
30°-40°	1316.0	26.2
40°-50°	1063.9	21.2
50°-60°	369.0	7.4
60°-70°	50.5	1.0
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2216.9	44.2
0°-40°	3532.9	70.4
0°-60°	4965.9	99.0
0°-90°	5017.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5017.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2906	
5°	2892	274
15°	2769	781
25°	2529	1162
35°	2114	1316
45°	1418	1064
55°	376	369
65°	43	50
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P246479

CATALOG NUMBER: LD8B50D010 ER8B50835 8LBS0B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2906.3
2.5°	2902.8
5°	2892.1
7.5°	2870.7
10°	2844.0
12.5°	2808.4
15°	2769.3
17.5°	2719.5
20°	2664.3
22.5°	2600.2
25°	2529.0
27.5°	2443.6
30°	2345.7
32.5°	2235.4
35°	2114.3
37.5°	1980.9
40°	1831.4
42.5°	1648.1
45°	1418.5
47.5°	1140.8
50°	852.5
52.5°	583.8
55°	375.5
57.5°	222.5
60°	129.9
62.5°	76.5
65°	42.7
67.5°	19.6
70°	5.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)