

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243815

Luminaire Tested: **LD8B50D010 ER8B50835 8LBW0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243815
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B50D010 ER8B50835 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3500 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5809.0 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243815

CATALOG NUMBER: LD8B50D010 ER8B50835 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243815

CATALOG NUMBER: LD8B50D010 ER8B50835 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | | 106 | 106 | 106 | | 102 | 102 | 102 | 100 |
| 1 | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 | | 100 | 98 | 97 | | 96 | 95 | 94 | 92 |
| 2 | 106 | 101 | 97 | 93 | 104 | 99 | 95 | 92 | 96 | 93 | 90 | | 93 | 90 | 88 | | 90 | 88 | 86 | 84 |
| 3 | 100 | 93 | 87 | 83 | 98 | 92 | 86 | 82 | 89 | 85 | 81 | | 86 | 83 | 80 | | 84 | 81 | 78 | 77 |
| 4 | 94 | 86 | 79 | 75 | 92 | 84 | 79 | 74 | 82 | 77 | 73 | | 80 | 76 | 72 | | 78 | 75 | 72 | 70 |
| 5 | 88 | 79 | 72 | 68 | 87 | 78 | 72 | 67 | 76 | 71 | 67 | | 74 | 70 | 66 | | 73 | 69 | 65 | 64 |
| 6 | 83 | 73 | 66 | 62 | 82 | 72 | 66 | 61 | 71 | 65 | 61 | | 69 | 64 | 60 | | 68 | 63 | 60 | 58 |
| 7 | 78 | 68 | 61 | 56 | 77 | 67 | 61 | 56 | 66 | 60 | 56 | | 64 | 59 | 55 | | 63 | 59 | 55 | 54 |
| 8 | 74 | 63 | 56 | 52 | 72 | 62 | 56 | 52 | 61 | 55 | 51 | | 60 | 55 | 51 | | 59 | 54 | 51 | 49 |
| 9 | 70 | 59 | 52 | 48 | 68 | 58 | 52 | 47 | 57 | 51 | 47 | | 56 | 51 | 47 | | 55 | 50 | 47 | 45 |
| 10 | 66 | 55 | 48 | 44 | 65 | 54 | 48 | 44 | 53 | 48 | 44 | | 53 | 47 | 44 | | 52 | 47 | 43 | 42 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 103064 |
| 5° | 106114 |
| 10° | 114956 |
| 15° | 125778 |
| 20° | 130854 |
| 25° | 130374 |
| 30° | 122291 |
| 35° | 102547 |
| 40° | 71398 |
| 45° | 40892 |
| 50° | 21957 |
| 55° | 9059 |
| 60° | 2257 |
| 65° | 576 |
| 70° | 289 |
| 75° | 191 |
| 80° | 284 |
| 85° | 0 |



TEST NUMBER: P243815

CATALOG NUMBER: LD8B50D010 ER8B50835 8LBW0LI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 335.1 | 5.8 |
| 10°-20° | 1110.4 | 19.1 |
| 20°-30° | 1747.2 | 30.1 |
| 30°-40° | 1662.0 | 28.6 |
| 40°-50° | 766.2 | 13.2 |
| 50°-60° | 174.1 | 3.0 |
| 60°-70° | 11.5 | 0.2 |
| 70°-80° | 2.3 | 0.0 |
| 80°-90° | 0.2 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 3192.8 | 55.0 |
| 0°-40° | 4854.7 | 83.6 |
| 0°-60° | 5795.0 | 99.8 |
| 0°-90° | 5809.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 5809.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 3342 | |
| 5° | 3428 | 335 |
| 15° | 3940 | 1110 |
| 25° | 3832 | 1747 |
| 35° | 2724 | 1662 |
| 45° | 938 | 766 |
| 55° | 168 | 174 |
| 65° | 8 | 11 |
| 75° | 2 | 2 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P243815

CATALOG NUMBER: LD8B50D010 ER8B50835 8LBW0LI

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 3342.3 |
| 1° | 3340.7 |
| 2° | 3347.1 |
| 3° | 3366.2 |
| 4° | 3394.8 |
| 5° | 3428.1 |
| 6° | 3469.5 |
| 7° | 3514.0 |
| 8° | 3560.1 |
| 9° | 3614.1 |
| 10° | 3671.3 |
| 11° | 3728.5 |
| 12° | 3788.9 |
| 13° | 3846.1 |
| 14° | 3898.6 |
| 15° | 3939.9 |
| 16° | 3970.1 |
| 17° | 3990.8 |
| 18° | 4000.3 |
| 19° | 3998.7 |
| 20° | 3987.6 |
| 21° | 3968.5 |
| 22° | 3944.7 |
| 23° | 3912.9 |
| 24° | 3876.3 |
| 25° | 3831.8 |
| 26° | 3779.4 |
| 27° | 3712.6 |
| 28° | 3633.2 |
| 29° | 3541.0 |
| 30° | 3434.5 |
| 32.5° | 3115.0 |
| 35° | 2724.1 |
| 37.5° | 2269.5 |
| 40° | 1773.7 |
| 42.5° | 1311.2 |
| 45° | 937.7 |
| 47.5° | 664.3 |
| 50° | 457.7 |
| 52.5° | 292.4 |
| 55° | 168.5 |
| 57.5° | 84.2 |
| 60° | 36.6 |
| 62.5° | 14.3 |
| 65° | 7.9 |



TEST NUMBER: P243815

CATALOG NUMBER: LD8B50D010 ER8B50835 8LBW0LI

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|-----|
| 67.5° | 4.8 |
| 70° | 3.2 |
| 72.5° | 3.2 |
| 75° | 1.6 |
| 77.5° | 1.6 |
| 80° | 1.6 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)