

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250858

Luminaire Tested: **LD8B60D010 ER8B60950 8LBMOLI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250858  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-11)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B60D010 ER8B60950 8LBM0LI  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
90 CRI 5000 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5966.0 lumens  
Efficiency: N/A  
Efficacy: 100.3 lumens/watt  
Spacing Criteria (0/90/45): 0.63 / 0.63 / 0.72  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250858

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBM0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P250858

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBM0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	73	80	75	72		79	75	72		77	74	71	70
7	86	78	72	69	85	77	72	68	76	71	68		75	71	68		74	70	67	66
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	60	59
10	76	67	62	58	75	67	61	58	66	61	58		65	61	58		64	60	58	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	320932
5°	307139
10°	273432
15°	219663
20°	172044
25°	138910
30°	107639
35°	61307
40°	23126
45°	9973
50°	4015
55°	1500
60°	802
65°	540
70°	334
75°	226
80°	0
85°	0



TEST NUMBER: P250858

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBM0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	910.7	15.3
10°-20°	1910.7	32.0
20°-30°	1869.7	31.3
30°-40°	1034.4	17.3
40°-50°	200.2	3.4
50°-60°	30.7	0.5
60°-70°	7.6	0.1
70°-80°	2.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4691.1	78.6
0°-40°	5725.6	96.0
0°-60°	5956.5	99.8
0°-90°	5966.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5966.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10408	
5°	9922	911
15°	6881	1911
25°	4083	1870
35°	1629	1034
45°	229	200
55°	28	31
65°	7	8
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P250858

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBM0LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	10407.6
2.5°	10264.4
5°	9922.4
7.5°	9442.7
10°	8732.5
12.5°	7834.5
15°	6880.8
17.5°	5986.5
20°	5242.8
22.5°	4627.5
25°	4082.7
27.5°	3569.6
30°	3023.0
32.5°	2381.6
35°	1628.6
37.5°	979.8
40°	574.5
42.5°	358.8
45°	228.7
47.5°	143.2
50°	83.7
52.5°	46.5
55°	27.9
57.5°	16.7
60°	13.0
62.5°	9.3
65°	7.4
67.5°	5.6
70°	3.7
72.5°	1.9
75°	1.9
77.5°	1.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)