

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245333

Luminaire Tested: **LD8B50D010 ER8B50840 8LBS0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245333
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B50D010 ER8B50840 8LBS0WH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 4000 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6108.9 lumens
Efficiency: N/A
Efficacy: 115.3 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245333

CATALOG NUMBER: LD8B50D010 ER8B50840 8LBS0WH

Luminous Intensity Polar Plot





TEST NUMBER: P245333

CATALOG NUMBER: LD8B50D010 ER8B50840 8LBS0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70		77	73	69		75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57		66	60	56		64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51		61	55	51		60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47		56	51	47		55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43		52	47	43		51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39		49	43	39		48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	106700
5°	107107
10°	108459
15°	110579
20°	112156
25°	112616
30°	109167
35°	99640
40°	86192
45°	67851
50°	43770
55°	21483
60°	8832
65°	3867
70°	1118
75°	417
80°	320
85°	0



TEST NUMBER: P245333

CATALOG NUMBER: LD8B50D010 ER8B50840 8LBS0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	330.4	5.4
10°-20°	978.9	16.0
20°-30°	1515.5	24.8
30°-40°	1641.8	26.9
40°-50°	1181.4	19.3
50°-60°	395.3	6.5
60°-70°	59.7	1.0
70°-80°	5.1	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2824.8	46.2
0°-40°	4466.7	73.1
0°-60°	6043.4	98.9
0°-90°	6108.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6108.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3460	
5°	3460	330
15°	3464	979
25°	3310	1516
35°	2647	1642
45°	1556	1181
55°	400	395
65°	53	60
75°	4	5
85°	0	1
90°	0	



TEST NUMBER: P245333

CATALOG NUMBER: LD8B50D010 ER8B50840 8LBS0WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3460.2
2.5°	3460.2
5°	3460.2
7.5°	3462.0
10°	3463.8
12.5°	3467.3
15°	3463.8
17.5°	3449.6
20°	3417.8
22.5°	3370.0
25°	3309.9
27.5°	3214.4
30°	3065.9
32.5°	2871.4
35°	2646.9
37.5°	2404.6
40°	2141.2
42.5°	1858.3
45°	1555.9
47.5°	1228.8
50°	912.4
52.5°	625.9
55°	399.6
57.5°	238.7
60°	143.2
62.5°	86.6
65°	53.0
67.5°	26.5
70°	12.4
72.5°	5.3
75°	3.5
77.5°	3.5
80°	1.8
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)