

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251050

Luminaire Tested: **LD8B60D010 ER8B60950 8LBN0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251050  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201884)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B60D010 ER8B60950 8LBN0WMH  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
90 CRI 5000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5055.0 lumens  
Efficiency: N/A  
Efficacy: 85.0 lumens/watt  
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251050

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBN0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P251050

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBN0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93		96	94	91		93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86		91	88	85		89	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80		86	82	79		84	81	79	77
5	94	86	80	76	92	85	80	76	83	78	75		81	77	74		80	76	74	72
6	89	81	75	71	88	80	75	71	79	74	70		77	73	70		76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66		73	69	66		72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62		70	65	62		69	65	62	60
9	78	68	63	59	77	68	63	59	67	62	59		66	62	59		65	61	58	57
10	74	65	59	56	73	65	59	56	64	59	56		63	59	55		62	58	55	54

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	227011
5°	223845
10°	204812
15°	175848
20°	148076
25°	122313
30°	91766
35°	54697
40°	26052
45°	11351
50°	5123
55°	2247
60°	1332
65°	730
70°	757
75°	0
80°	284
85°	1238



TEST NUMBER: P251050

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBN0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	667.8	13.2
10°-20°	1534.9	30.4
20°-30°	1628.5	32.2
30°-40°	929.2	18.4
40°-50°	230.3	4.6
50°-60°	45.2	0.9
60°-70°	13.5	0.3
70°-80°	3.0	0.1
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3831.2	75.8
0°-40°	4760.4	94.2
0°-60°	5035.9	99.6
0°-90°	5055.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5055.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7362	
5°	7232	668
15°	5508	1535
25°	3595	1628
35°	1453	929
45°	260	230
55°	42	45
65°	10	14
75°	0	3
85°	4	2
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251050

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBN0WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7361.8
2.5°	7358.3
5°	7231.5
7.5°	6952.9
10°	6541.0
12.5°	6043.8
15°	5508.3
17.5°	4997.9
20°	4512.4
22.5°	4045.5
25°	3594.9
27.5°	3111.1
30°	2577.2
32.5°	2003.4
35°	1453.0
37.5°	1001.0
40°	647.2
42.5°	410.4
45°	260.3
47.5°	170.3
50°	106.8
52.5°	64.9
55°	41.8
57.5°	33.5
60°	21.6
62.5°	20.0
65°	10.0
67.5°	10.0
70°	8.4
72.5°	4.9
75°	0.0
77.5°	1.6
80°	1.6
82.5°	3.5
85°	3.5
87.5°	1.6
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251050

CATALOG NUMBER: LD8B60D010 ER8B60950 8LBN0WMH

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)