

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244685

Luminaire Tested: **LD8B50D010 ER8B50840 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244685
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B50D010 ER8B50840 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 4000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5320.0 lumens
Efficiency: N/A
Efficacy: 100.4 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244685

CATALOG NUMBER: LD8B50D010 ER8B50840 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244685

CATALOG NUMBER: LD8B50D010 ER8B50840 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79		85	81	78		82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64		73	68	64		71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59		67	62	58		66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49		58	53	49		57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46		55	49	45		54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42		51	46	42		51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	118886
5°	116496
10°	112808
15°	111287
20°	110624
25°	109224
30°	103352
35°	85245
40°	53228
45°	34229
50°	26543
55°	20435
60°	15480
65°	10062
70°	4301
75°	2109
80°	941
85°	637



TEST NUMBER: P244685

CATALOG NUMBER: LD8B50D010 ER8B50840 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	354.0	6.7
10°-20°	984.9	18.5
20°-30°	1466.9	27.6
30°-40°	1362.3	25.6
40°-50°	643.5	12.1
50°-60°	345.7	6.5
60°-70°	138.8	2.6
70°-80°	21.8	0.4
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2805.7	52.7
0°-40°	4168.0	78.3
0°-60°	5157.2	96.9
0°-90°	5320.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5320.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3855	
5°	3764	354
15°	3486	985
25°	3210	1467
35°	2264	1362
45°	785	643
55°	380	346
65°	138	139
75°	18	22
85°	2	2
90°	0	



TEST NUMBER: P244685

CATALOG NUMBER: LD8B50D010 ER8B50840 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3855.4
2.5°	3828.9
5°	3763.5
7.5°	3680.4
10°	3602.7
12.5°	3539.0
15°	3486.0
17.5°	3431.2
20°	3371.1
22.5°	3302.1
25°	3210.2
27.5°	3081.2
30°	2902.6
32.5°	2641.0
35°	2264.5
37.5°	1783.6
40°	1322.3
42.5°	984.6
45°	784.9
47.5°	655.8
50°	553.3
52.5°	461.4
55°	380.1
57.5°	309.4
60°	251.0
62.5°	196.2
65°	137.9
67.5°	81.3
70°	47.7
72.5°	28.3
75°	17.7
77.5°	10.6
80°	5.3
82.5°	3.5
85°	1.8
87.5°	0.0
90°	0.0

(END OF REPORT)