

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243899

Luminaire Tested: **LD8B50D010 ER8B50850 8LBNOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243899
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-10)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B50D010 ER8B50850 8LBN0LI
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 5000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5316.0 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.32
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243899

CATALOG NUMBER: LD8B50D010 ER8B50850 8LBN0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243899

CATALOG NUMBER: LD8B50D010 ER8B50850 8LBN0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	99	101	99	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	91		94	92	89		92	90	88	87
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		89	86	84	83
5	98	91	86	83	96	90	86	82	88	85	82		87	84	81		85	83	80	79
6	94	87	82	79	93	86	82	78	85	81	78		83	80	77		82	79	77	76
7	91	83	78	75	90	83	78	75	81	77	74		80	77	74		79	76	74	72
8	88	80	75	72	86	79	75	71	78	74	71		77	74	71		76	73	71	70
9	85	77	72	69	84	76	72	69	75	71	68		75	71	68		74	70	68	67
10	82	74	69	66	81	73	69	66	73	69	66		72	68	66		71	68	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	803129
5°	557815
10°	293534
15°	185722
20°	138018
25°	108506
30°	78121
35°	33526
40°	11682
45°	4483
50°	1036
55°	387
60°	0
65°	525
70°	162
75°	429
80°	639
85°	0



TEST NUMBER: P243899

CATALOG NUMBER: LD8B50D010 ER8B50850 8LBN0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1444.7	27.2
10°-20°	1678.6	31.6
20°-30°	1448.7	27.3
30°-40°	628.5	11.8
40°-50°	98.5	1.9
50°-60°	7.1	0.1
60°-70°	3.8	0.1
70°-80°	4.0	0.1
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4572.0	86.0
0°-40°	5200.6	97.8
0°-60°	5306.2	99.8
0°-90°	5316.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5316.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	26045	
5°	18021	###
15°	5818	1679
25°	3189	1449
35°	891	629
45°	103	99
55°	7	7
65°	7	4
75°	4	4
85°	0	2
90°	0	



TEST NUMBER: P243899

CATALOG NUMBER: LD8B50D010 ER8B50850 8LBN0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	26044.9
2.5°	23519.2
5°	18020.7
7.5°	12852.1
10°	9374.5
12.5°	7193.1
15°	5817.6
17.5°	4892.8
20°	4205.9
22.5°	3620.0
25°	3189.1
27.5°	2734.8
30°	2194.0
32.5°	1525.2
35°	890.6
37.5°	497.6
40°	290.2
42.5°	180.3
45°	102.8
47.5°	82.9
50°	21.6
52.5°	10.8
55°	7.2
57.5°	3.6
60°	0.0
62.5°	1.8
65°	7.2
67.5°	5.4
70°	1.8
72.5°	9.0
75°	3.6
77.5°	0.0
80°	3.6
82.5°	1.8
85°	0.0
87.5°	3.6
90°	0.0

(END OF REPORT)