

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246635

Luminaire Tested: **LD8B50D010 ER8B50850 8LBN0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246635
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201839)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B50D010 ER8B50850 8LBN0MW
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 5000 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5135.0 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.85
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246635

CATALOG NUMBER: LD8B50D010 ER8B50850 8LBN0MW

Luminous Intensity Polar Plot





TEST NUMBER: P246635

CATALOG NUMBER: LD8B50D010 ER8B50850 8LBN0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67
5	87	78	71	66	85	77	70	65	75	69	65	73	68	64	71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60	68	63	59	67	62	59	57
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	166054
5°	164865
10°	150238
15°	128775
20°	114125
25°	101841
30°	82244
35°	57065
40°	36208
45°	26898
50°	22955
55°	20128
60°	18008
65°	16089
70°	13867
75°	12760
80°	11880
85°	10473



TEST NUMBER: P246635

CATALOG NUMBER: LD8B50D010 ER8B50850 8LBN0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	491.3	9.6
10°-20°	1136.3	22.1
20°-30°	1351.2	26.3
30°-40°	955.2	18.6
40°-50°	493.1	9.6
50°-60°	338.1	6.6
60°-70°	219.4	4.3
70°-80°	115.1	2.2
80°-90°	35.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2978.8	58.0
0°-40°	3934.0	76.6
0°-60°	4765.1	92.8
0°-90°	5135.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5135.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5385	
5°	5326	491
15°	4034	1136
25°	2993	1351
35°	1516	955
45°	617	493
55°	374	338
65°	220	219
75°	107	115
85°	30	33
90°	0	2
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P246635

CATALOG NUMBER: LD8B50D010 ER8B50850 8LBN0MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5385.0
2.5°	5385.0
5°	5326.1
7.5°	5130.2
10°	4798.1
12.5°	4401.9
15°	4033.8
17.5°	3730.9
20°	3477.8
22.5°	3238.5
25°	2993.2
27.5°	2685.4
30°	2309.8
32.5°	1905.8
35°	1515.9
37.5°	1168.0
40°	899.5
42.5°	723.8
45°	616.8
47.5°	539.0
50°	478.5
52.5°	425.5
55°	374.4
57.5°	329.3
60°	292.0
62.5°	253.1
65°	220.5
67.5°	191.1
70°	153.8
72.5°	132.1
75°	107.1
77.5°	86.9
80°	66.9
82.5°	49.8
85°	29.6
87.5°	17.1
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P246635

CATALOG NUMBER: LD8B50D010 ER8B50850 8LBN0MW

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)