

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244043

Luminaire Tested: **LD8B50D010 ER8B50850 8LBSOLI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244043  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-12)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B50D010 ER8B50850 8LBSOLI  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 5000 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6286.0 lumens  
Efficiency: N/A  
Efficacy: 118.6 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.24  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 53  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244043

CATALOG NUMBER: LD8B50D010 ER8B50850 8LBSOLI

### Luminous Intensity Polar Plot





TEST NUMBER: P244043

CATALOG NUMBER: LD8B50D010 ER8B50850 8LBSOLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	99	95	91	103	98	93	90	94	91	88		91	88	86		88	86	84	82
3	98	91	85	80	96	89	84	79	86	82	78		84	80	77		82	78	75	74
4	92	83	76	71	90	82	75	71	79	74	70		77	73	69		75	71	68	66
5	86	76	69	63	84	75	68	63	73	67	63		71	66	62		69	65	61	60
6	80	70	62	57	79	69	62	57	67	61	56		66	60	56		64	59	56	54
7	75	64	57	52	74	63	56	52	62	56	51		61	55	51		59	54	51	49
8	71	59	52	47	69	58	52	47	57	51	47		56	51	46		55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43		52	47	43		51	46	42	41
10	62	51	44	39	61	50	44	39	50	43	39		49	43	39		48	43	39	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	108075
5°	108544
10°	110306
15°	113098
20°	115070
25°	115199
30°	111634
35°	102208
40°	88828
45°	70289
50°	45579
55°	22779
60°	9559
65°	4210
70°	1298
75°	643
80°	639
85°	637



TEST NUMBER: P244043

CATALOG NUMBER: LD8B50D010 ER8B50850 8LBSOLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	335.2	5.3
10°-20°	1001.1	15.9
20°-30°	1550.8	24.7
30°-40°	1684.2	26.8
40°-50°	1223.9	19.5
50°-60°	415.9	6.6
60°-70°	66.3	1.1
70°-80°	7.1	0.1
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2887.1	45.9
0°-40°	4571.3	72.7
0°-60°	6211.1	98.8
0°-90°	6286.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6286.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3505	
5°	3507	335
15°	3543	1001
25°	3386	1551
35°	2715	1684
45°	1612	1224
55°	424	416
65°	58	66
75°	5	7
85°	2	1
90°	0	



TEST NUMBER: P244043

CATALOG NUMBER: LD8B50D010 ER8B50850 8LBSOLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3504.8
2.5°	3504.8
5°	3506.6
7.5°	3512.0
10°	3522.8
12.5°	3535.4
15°	3542.7
17.5°	3535.4
20°	3506.6
22.5°	3454.3
25°	3385.8
27.5°	3283.0
30°	3135.2
32.5°	2938.7
35°	2715.1
37.5°	2471.7
40°	2206.7
42.5°	1920.1
45°	1611.8
47.5°	1280.0
50°	950.1
52.5°	650.8
55°	423.7
57.5°	257.8
60°	155.0
62.5°	95.6
65°	57.7
67.5°	32.5
70°	14.4
72.5°	9.0
75°	5.4
77.5°	3.6
80°	3.6
82.5°	1.8
85°	1.8
87.5°	0.0
90°	0.0

(END OF REPORT)