

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250932

Luminaire Tested: **LD8B60D010 ER8B609727 8LBW0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250932
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27940)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B609727 8LBW0H
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4353.1 lumens
Efficiency: N/A
Efficacy: 73.2 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.12
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250932

CATALOG NUMBER: LD8B60D010 ER8B609727 8LBW0H

Luminous Intensity Polar Plot





TEST NUMBER: P250932

CATALOG NUMBER: LD8B60D010 ER8B609727 8LBW0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	95	93	92
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83	79	77	75
4	93	84	78	73	91	83	77	72	81	75	71		79	74	71		77	73	70	68
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71	67	63	62
6	82	71	65	60	80	71	64	59	69	63	59		68	62	58		66	62	58	56
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		62	57	53	52
8	72	61	54	50	71	61	54	50	60	54	49		58	53	49		57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46		55	49	45		54	49	45	44
10	64	53	47	42	63	53	47	42	52	46	42		51	46	42		50	45	42	40

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250932

CATALOG NUMBER: LD8B60D010 ER8B609727 8LBW0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	275.0	6.3
10°-20°	789.2	18.1
20°-30°	1187.7	27.3
30°-40°	1175.9	27.0
40°-50°	597.5	13.7
50°-60°	240.7	5.5
60°-70°	72.9	1.7
70°-80°	12.6	0.3
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2251.9	51.7
0°-40°	3427.8	78.7
0°-60°	4266.0	98.0
0°-90°	4353.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4353.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2919	
5°	2901	275
15°	2798	789
25°	2594	1188
35°	1935	1176
45°	732	597
55°	259	241
65°	67	73
75°	10	13
85°	1	2
90°	0	



TEST NUMBER: P250932

CATALOG NUMBER: LD8B60D010 ER8B609727 8LBW0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2918.9
1°	2912.6
2°	2907.5
3°	2906.3
4°	2905.0
5°	2901.2
6°	2896.2
7°	2886.1
8°	2871.1
9°	2857.2
10°	2842.1
11°	2829.5
12°	2820.7
13°	2814.4
14°	2806.9
15°	2798.1
16°	2786.8
17°	2772.9
18°	2756.6
19°	2737.7
20°	2716.3
21°	2693.7
22°	2671.0
23°	2647.1
24°	2621.9
25°	2594.3
26°	2564.1
27°	2525.1
28°	2479.8
29°	2425.7
30°	2362.8
32.5°	2179.1
35°	1935.0
37.5°	1630.5
40°	1290.8
42.5°	975.1
45°	732.2
47.5°	559.9
50°	439.1
52.5°	341.0
55°	259.2
57.5°	192.5
60°	144.7
62.5°	103.2
65°	66.7



TEST NUMBER: P250932

CATALOG NUMBER: LD8B60D010 ER8B609727 8LBW0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	41.5
70°	26.4
72.5°	16.4
75°	10.1
77.5°	6.3
80°	3.8
82.5°	2.5
85°	1.3
87.5°	0.0
90°	0.0

(END OF REPORT)