

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250958

Luminaire Tested: **LD8B60D010 ER8B609730 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250958
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27944)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B609730 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4161.0 lumens
Efficiency: N/A
Efficacy: 69.9 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250958

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P250958

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	86	83	82
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	69	67
7	85	76	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	58		64	60	57	56
10	74	64	59	55	73	64	58	55	63	58	55		62	58	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250958

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	534.1	12.8
10°-20°	1193.7	28.7
20°-30°	1357.2	32.6
30°-40°	797.0	19.2
40°-50°	213.9	5.1
50°-60°	50.8	1.2
60°-70°	11.6	0.3
70°-80°	2.6	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3085.0	74.1
0°-40°	3882.0	93.3
0°-60°	4146.7	99.7
0°-90°	4161.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4161.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6352	
5°	5902	534
15°	4269	1194
25°	2995	1357
35°	1241	797
45°	256	214
55°	51	51
65°	11	12
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P250958

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBN0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	6351.8
1°	6316.7
2°	6252.0
3°	6160.7
4°	6042.6
5°	5902.1
6°	5743.3
7°	5563.5
8°	5383.6
9°	5202.3
10°	5029.4
11°	4860.8
12°	4702.0
13°	4554.5
14°	4406.9
15°	4269.2
16°	4134.3
17°	4000.8
18°	3871.5
19°	3740.8
20°	3612.9
21°	3485.1
22°	3362.8
23°	3242.0
24°	3118.3
25°	2994.6
26°	2866.7
27°	2727.6
28°	2581.5
29°	2421.3
30°	2248.4
32.5°	1763.6
35°	1240.9
37.5°	817.9
40°	535.4
42.5°	369.6
45°	255.8
47.5°	175.7
50°	116.6
52.5°	75.9
55°	50.6
57.5°	33.7
60°	22.5
62.5°	15.5
65°	11.2



TEST NUMBER: P250958

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBN0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	7.0
70°	4.2
72.5°	2.8
75°	2.8
77.5°	1.4
80°	1.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)