

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251450

Luminaire Tested: **LD8B60D010 ER8B609730 8LBN0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251450
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201839)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B609730 8LBN0MW
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 3000 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4746.0 lumens
Efficiency: N/A
Efficacy: 79.8 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.85
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251450

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBN0MW

Luminous Intensity Polar Plot





TEST NUMBER: P251450

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBN0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98		98	97	95		95	94	92	90
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	93	84	77	72	91	83	76	72	80	75	71		78	74	70		76	72	69	67
5	87	78	71	66	85	77	70	65	75	69	65		73	68	64		71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60		68	63	59		67	62	59	57
7	78	67	60	56	76	67	60	55	65	59	55		64	59	55		63	58	54	53
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59	54	51	49
9	70	59	53	48	69	59	52	48	58	52	48		57	51	48		56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53	48	45	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	153475
5°	152375
10°	138856
15°	119019
20°	105482
25°	94124
30°	76017
35°	52743
40°	33463
45°	24857
50°	21218
55°	18601
60°	16645
65°	14870
70°	12821
75°	11783
80°	10974
85°	9694



TEST NUMBER: P251450

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBN0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	454.1	9.6
10°-20°	1050.2	22.1
20°-30°	1248.9	26.3
30°-40°	882.9	18.6
40°-50°	455.7	9.6
50°-60°	312.5	6.6
60°-70°	202.8	4.3
70°-80°	106.3	2.2
80°-90°	32.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2753.1	58.0
0°-40°	3636.0	76.6
0°-60°	4404.2	92.8
0°-90°	4746.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4746.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4977	
5°	4923	454
15°	3728	1050
25°	2766	1249
35°	1401	883
45°	570	456
55°	346	312
65°	204	203
75°	99	106
85°	27	31
90°	0	2
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251450

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBN0MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	4977.1
2.5°	4977.1
5°	4922.6
7.5°	4741.6
10°	4434.6
12.5°	4068.4
15°	3728.2
17.5°	3448.3
20°	3214.4
22.5°	2993.1
25°	2766.4
27.5°	2482.0
30°	2134.9
32.5°	1761.5
35°	1401.1
37.5°	1079.5
40°	831.3
42.5°	669.0
45°	570.0
47.5°	498.2
50°	442.3
52.5°	393.3
55°	346.0
57.5°	304.4
60°	269.9
62.5°	233.9
65°	203.8
67.5°	176.6
70°	142.2
72.5°	122.1
75°	98.9
77.5°	80.3
80°	61.8
82.5°	46.0
85°	27.4
87.5°	15.8
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251450

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBN0MW

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)