

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245555

Luminaire Tested: **LD8B50D010 ER8B50850 8LBW0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245555
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B50D010 ER8B50850 8LBW0GPH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 5000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4993.0 lumens
Efficiency: N/A
Efficacy: 94.2 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245555

CATALOG NUMBER: LD8B50D010 ER8B50850 8LBW0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245555

CATALOG NUMBER: LD8B50D010 ER8B50850 8LBW0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92					92			
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84					84			
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76					76			
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70					70			
5	88	79	72	67	87	78	72	67	76	71	66	74	70	66	73	69	65	64					64			
6	83	73	66	61	82	72	66	61	71	65	61	69	64	60	68	63	60	58					58			
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55	54					54			
8	74	63	56	52	73	63	56	52	61	56	51	60	55	51	59	55	51	49					49			
9	70	59	52	48	69	58	52	48	57	52	48	57	51	47	56	51	47	46					46			
10	66	55	49	44	65	55	49	44	54	48	44	53	48	44	52	47	44	43					43			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	119885
5°	117053
10°	113381
15°	111744
20°	110427
25°	108057
30°	101209
35°	82640
40°	49335
45°	29632
50°	21357
55°	14537
60°	9115
65°	4473
70°	1136
75°	429
80°	320
85°	0



TEST NUMBER: P245555

CATALOG NUMBER: LD8B50D010 ER8B50850 8LBW0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	355.7	7.1
10°-20°	987.8	19.8
20°-30°	1450.6	29.1
30°-40°	1315.0	26.3
40°-50°	562.9	11.3
50°-60°	249.1	5.0
60°-70°	66.4	1.3
70°-80°	5.2	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2794.2	56.0
0°-40°	4109.1	82.3
0°-60°	4921.1	98.6
0°-90°	4993.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4993.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3888	
5°	3782	356
15°	3500	988
25°	3176	1451
35°	2195	1315
45°	680	563
55°	270	249
65°	61	66
75°	4	5
85°	0	0
90°	0	



TEST NUMBER: P245555

CATALOG NUMBER: LD8B50D010 ER8B50850 8LBW0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3887.8
2.5°	3857.2
5°	3781.5
7.5°	3694.9
10°	3621.0
12.5°	3559.8
15°	3500.3
17.5°	3437.2
20°	3365.1
22.5°	3280.4
25°	3175.9
27.5°	3035.3
30°	2842.4
32.5°	2572.0
35°	2195.3
37.5°	1701.5
40°	1225.6
42.5°	885.0
45°	679.5
47.5°	547.9
50°	445.2
52.5°	353.3
55°	270.4
57.5°	201.9
60°	147.8
62.5°	102.7
65°	61.3
67.5°	27.0
70°	12.6
72.5°	7.2
75°	3.6
77.5°	1.8
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)