

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251296

Luminaire Tested: **LD8B60D010 ER8B609730 8LBS0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251296
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-16)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B609730 8LBS0GPH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 3000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5104.1 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251296

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBS0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P251296

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBS0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91					91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81					81			
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73					73			
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65					65			
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58					58			
6	79	69	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53					53			
7	74	63	56	50	73	62	55	50	61	55	50	59	54	50	58	53	49	48					48			
8	70	58	51	46	68	57	50	46	56	50	45	55	49	45	54	49	45	43					43			
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	45	41	40					40			
10	62	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36					36			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	90341
5°	90067
10°	89180
15°	88264
20°	87338
25°	85911
30°	83558
35°	79753
40°	74152
45°	62610
50°	42509
55°	22209
60°	9966
65°	4859
70°	1956
75°	1191
80°	888
85°	601



TEST NUMBER: P251296

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBS0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	275.8	5.4
10°-20°	779.9	15.3
20°-30°	1160.9	22.7
30°-40°	1319.6	25.9
40°-50°	1079.1	21.1
50°-60°	402.3	7.9
60°-70°	73.5	1.4
70°-80°	11.4	0.2
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2216.5	43.4
0°-40°	3536.1	69.3
0°-60°	5017.5	98.3
0°-90°	5104.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5104.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2930	
5°	2910	276
15°	2765	780
25°	2525	1161
35°	2119	1320
45°	1436	1079
55°	413	402
65°	67	74
75°	10	11
85°	2	2
90°	0	



TEST NUMBER: P251296

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBS0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2929.7
2.5°	2924.7
5°	2909.7
7.5°	2883.1
10°	2848.1
12.5°	2808.1
15°	2764.8
17.5°	2714.8
20°	2661.5
22.5°	2598.2
25°	2525.0
27.5°	2441.7
30°	2346.7
32.5°	2238.5
35°	2118.6
37.5°	1990.3
40°	1842.1
42.5°	1658.9
45°	1435.7
47.5°	1167.5
50°	886.1
52.5°	624.6
55°	413.1
57.5°	259.8
60°	161.6
62.5°	103.3
65°	66.6
67.5°	38.3
70°	21.7
72.5°	13.3
75°	10.0
77.5°	6.7
80°	5.0
82.5°	1.7
85°	1.7
87.5°	0.0
90°	0.0

(END OF REPORT)