

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251006

Luminaire Tested: **LD8B60D010 ER8B609730 8LBS0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251006
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B609730 8LBS0H
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5037.0 lumens
Efficiency: N/A
Efficacy: 84.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251006

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBS0H

Luminous Intensity Polar Plot





TEST NUMBER: P251006

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBS0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81	78	75	73
4	91	82	75	70	89	81	75	70	79	73	69		76	72	68		74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62		70	65	61		69	64	60	59
6	80	69	61	56	78	68	61	56	66	60	56		65	59	55		63	58	55	53
7	75	63	56	51	73	63	56	51	61	55	50		60	54	50		59	54	50	48
8	70	58	51	46	68	58	51	46	57	50	46		55	50	46		54	49	45	44
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P251006

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBS0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	275.3	5.5
10°-20°	782.7	15.5
20°-30°	1170.8	23.2
30°-40°	1309.6	26.0
40°-50°	1027.4	20.4
50°-60°	374.9	7.4
60°-70°	76.4	1.5
70°-80°	16.4	0.3
80°-90°	3.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2228.8	44.2
0°-40°	3538.4	70.2
0°-60°	4940.7	98.1
0°-90°	5037.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5037.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2923	
5°	2902	275
15°	2773	783
25°	2550	1171
35°	2108	1310
45°	1361	1027
55°	383	375
65°	70	76
75°	15	16
85°	3	3
90°	0	



TEST NUMBER: P251006

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBS0H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2923.1
2.5°	2918.7
5°	2902.3
7.5°	2878.5
10°	2847.4
12.5°	2811.7
15°	2773.1
17.5°	2730.0
20°	2679.5
22.5°	2620.1
25°	2550.3
27.5°	2464.1
30°	2361.7
32.5°	2241.3
35°	2107.7
37.5°	1957.6
40°	1791.3
42.5°	1593.7
45°	1360.6
47.5°	1097.7
50°	824.4
52.5°	577.8
55°	383.2
57.5°	245.1
60°	157.4
62.5°	104.0
65°	69.8
67.5°	44.6
70°	28.2
72.5°	19.3
75°	14.9
77.5°	10.4
80°	7.4
82.5°	4.5
85°	3.0
87.5°	1.5
90°	0.0

(END OF REPORT)