

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244691

Luminaire Tested: **LD8B50D010 ER8B50850 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244691
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B50D010 ER8B50850 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 5000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5424.0 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244691

CATALOG NUMBER: LD8B50D010 ER8B50850 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244691

CATALOG NUMBER: LD8B50D010 ER8B50850 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121211
5°	118774
10°	115012
15°	113461
20°	112786
25°	111361
30°	105374
35°	86909
40°	54266
45°	34896
50°	27061
55°	20833
60°	15782
65°	10259
70°	4391
75°	2145
80°	959
85°	637



TEST NUMBER: P244691

CATALOG NUMBER: LD8B50D010 ER8B50850 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	360.9	6.7
10°-20°	1004.1	18.5
20°-30°	1495.6	27.6
30°-40°	1388.9	25.6
40°-50°	656.0	12.1
50°-60°	352.5	6.5
60°-70°	141.5	2.6
70°-80°	22.2	0.4
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2860.6	52.7
0°-40°	4249.5	78.3
0°-60°	5258.0	96.9
0°-90°	5424.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5424.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3931	
5°	3837	361
15°	3554	1004
25°	3273	1496
35°	2309	1389
45°	800	656
55°	388	352
65°	141	142
75°	18	22
85°	2	2
90°	0	



TEST NUMBER: P244691

CATALOG NUMBER: LD8B50D010 ER8B50850 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3930.8
2.5°	3903.8
5°	3837.1
7.5°	3752.4
10°	3673.1
12.5°	3608.2
15°	3554.1
17.5°	3498.3
20°	3437.0
22.5°	3366.7
25°	3273.0
27.5°	3141.4
30°	2959.4
32.5°	2692.6
35°	2308.7
37.5°	1818.5
40°	1348.1
42.5°	1003.9
45°	800.2
47.5°	668.7
50°	564.1
52.5°	470.4
55°	387.5
57.5°	315.4
60°	255.9
62.5°	200.1
65°	140.6
67.5°	82.9
70°	48.7
72.5°	28.8
75°	18.0
77.5°	10.8
80°	5.4
82.5°	3.6
85°	1.8
87.5°	0.0
90°	0.0

(END OF REPORT)