

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251230

Luminaire Tested: **LD8B60D010 ER8B609730 8LBW0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251230
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B609730 8LBW0GPH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 3000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4614.0 lumens
Efficiency: N/A
Efficacy: 77.5 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251230

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBW0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P251230

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBW0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70
5	88	79	72	67	87	78	72	67	76	71	66	74	70	66	73	69	65	64
6	83	73	66	61	82	72	66	61	71	65	61	69	64	60	68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55	54
8	74	63	56	52	73	63	56	52	61	56	51	60	55	51	59	55	51	49
9	70	59	52	48	69	58	52	48	57	52	48	57	51	47	56	51	47	46
10	66	55	49	44	65	55	49	44	54	48	44	53	48	44	52	47	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	110786
5°	108166
10°	104776
15°	103262
20°	102046
25°	99854
30°	93525
35°	76369
40°	45592
45°	27382
50°	19736
55°	13430
60°	8424
65°	4130
70°	1055
75°	393
80°	302
85°	0



TEST NUMBER: P251230

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBW0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.7	7.1
10°-20°	912.8	19.8
20°-30°	1340.5	29.1
30°-40°	1215.2	26.3
40°-50°	520.2	11.3
50°-60°	230.2	5.0
60°-70°	61.4	1.3
70°-80°	4.8	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2582.1	56.0
0°-40°	3797.2	82.3
0°-60°	4547.6	98.6
0°-90°	4614.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4614.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3593	
5°	3494	329
15°	3235	913
25°	2935	1340
35°	2029	1215
45°	628	520
55°	250	230
65°	57	61
75°	3	5
85°	0	0
90°	0	



TEST NUMBER: P251230

CATALOG NUMBER: LD8B60D010 ER8B609730 8LBW0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3592.7
2.5°	3564.4
5°	3494.4
7.5°	3414.5
10°	3346.2
12.5°	3289.6
15°	3234.6
17.5°	3176.3
20°	3109.7
22.5°	3031.4
25°	2934.8
27.5°	2804.9
30°	2626.6
32.5°	2376.8
35°	2028.7
37.5°	1572.3
40°	1132.6
42.5°	817.8
45°	627.9
47.5°	506.3
50°	411.4
52.5°	326.5
55°	249.8
57.5°	186.5
60°	136.6
62.5°	94.9
65°	56.6
67.5°	25.0
70°	11.7
72.5°	6.7
75°	3.3
77.5°	1.7
80°	1.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)