

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244445

Luminaire Tested: **LD8B50D010 ER8B50930 8LBM0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244445
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27951)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B50D010 ER8B50930 8LBM0H
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4480.7 lumens
Efficiency: N/A
Efficacy: 84.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244445

CATALOG NUMBER: LD8B50D010 ER8B50930 8LBM0H

Luminous Intensity Polar Plot





TEST NUMBER: P244445

CATALOG NUMBER: LD8B50D010 ER8B50930 8LBM0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86	83	80	79
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80	77	74	73
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75	72	69	67
6	85	76	70	65	84	75	69	65	74	68	64		72	68	64		71	67	64	62
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67	62	59	58
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63	58	55	54
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59	55	51	50
10	69	59	53	49	68	58	53	49	58	52	48		57	52	48		56	51	48	47

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244445

CATALOG NUMBER: LD8B50D010 ER8B50930 8LBM0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	413.5	9.2
10°-20°	1040.9	23.2
20°-30°	1388.9	31.0
30°-40°	1070.6	23.9
40°-50°	399.2	8.9
50°-60°	130.5	2.9
60°-70°	30.1	0.7
70°-80°	6.1	0.1
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2843.3	63.5
0°-40°	3913.9	87.4
0°-60°	4443.6	99.2
0°-90°	4480.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4480.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4695	
5°	4479	414
15°	3703	1041
25°	3057	1389
35°	1742	1071
45°	485	399
55°	137	131
65°	27	30
75°	5	6
85°	1	1
90°	0	



TEST NUMBER: P244445

CATALOG NUMBER: LD8B50D010 ER8B50930 8LBM0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	4695.1
1°	4674.8
2°	4640.5
3°	4596.7
4°	4543.1
5°	4478.8
6°	4406.1
7°	4322.6
8°	4233.7
9°	4141.6
10°	4057.1
11°	3975.7
12°	3899.7
13°	3830.1
14°	3765.9
15°	3702.8
16°	3638.5
17°	3576.4
18°	3512.2
19°	3449.1
20°	3388.1
21°	3324.9
22°	3263.9
23°	3199.7
24°	3132.2
25°	3057.3
26°	2974.9
27°	2883.9
28°	2783.2
29°	2670.9
30°	2547.7
32.5°	2187.0
35°	1741.7
37.5°	1289.9
40°	913.2
42.5°	654.1
45°	484.9
47.5°	365.0
50°	269.7
52.5°	192.7
55°	137.0
57.5°	94.2
60°	62.1
62.5°	40.7
65°	26.8



TEST NUMBER: P244445

CATALOG NUMBER: LD8B50D010 ER8B50930 8LBM0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	18.2
70°	11.8
72.5°	7.5
75°	5.4
77.5°	3.3
80°	2.1
82.5°	1.1
85°	1.1
87.5°	0.0
90°	0.0

(END OF REPORT)