

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246605

Luminaire Tested: **LD8B50D010 ER8B50930 8LBW0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246605
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-48)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B50D010 ER8B50930 8LBW0MW
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4634.2 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246605

CATALOG NUMBER: LD8B50D010 ER8B50930 8LBW0MW

Luminous Intensity Polar Plot





TEST NUMBER: P246605

CATALOG NUMBER: LD8B50D010 ER8B50930 8LBW0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84		88	85	82		86	83	80	78
3	96	88	81	76	94	86	80	75	83	78	74		81	76	73		78	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66		74	69	65		72	68	64	62
5	84	73	66	60	82	72	65	60	70	64	59		68	63	59		67	62	58	56
6	79	67	60	54	77	66	59	54	65	58	54		63	58	53		62	57	53	51
7	74	62	55	49	72	61	54	49	60	54	49		59	53	49		57	52	48	47
8	69	58	50	45	68	57	50	45	56	50	45		55	49	45		54	48	45	43
9	65	54	47	42	64	53	46	42	52	46	41		51	45	41		50	45	41	40
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P246605

CATALOG NUMBER: LD8B50D010 ER8B50930 8LBW0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	282.9	6.1
10°-20°	779.2	16.8
20°-30°	1142.7	24.7
30°-40°	1044.5	22.5
40°-50°	517.1	11.2
50°-60°	382.4	8.3
60°-70°	294.0	6.3
70°-80°	153.2	3.3
80°-90°	38.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2204.8	47.6
0°-40°	3249.3	70.1
0°-60°	4148.9	89.5
0°-90°	4634.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4634.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3070	
5°	3007	283
15°	2759	779
25°	2502	1143
35°	1733	1045
45°	628	517
55°	423	382
65°	300	294
75°	143	153
85°	32	38
90°	0	



TEST NUMBER: P246605

CATALOG NUMBER: LD8B50D010 ER8B50930 8LBW0MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3070.5
2.5°	3054.3
5°	3007.3
7.5°	2944.1
10°	2879.4
12.5°	2816.2
15°	2758.9
17.5°	2704.5
20°	2645.7
22.5°	2579.5
25°	2501.6
27.5°	2394.3
30°	2244.5
32.5°	2034.3
35°	1733.0
37.5°	1359.5
40°	1003.9
42.5°	759.9
45°	627.6
47.5°	555.6
50°	502.7
52.5°	460.1
55°	423.3
57.5°	392.5
60°	366.0
62.5°	338.1
65°	299.9
67.5°	258.7
70°	217.6
72.5°	179.4
75°	142.6
77.5°	110.2
80°	80.8
82.5°	55.8
85°	32.3
87.5°	11.8
90°	0.0

(END OF REPORT)