

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250819

Luminaire Tested: **LD8B70D010 ER8B70830 8LBNOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250819
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-10)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B70D010 ER8B70830 8LBN0LI
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6902.0 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.32
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250819

CATALOG NUMBER: LD8B70D010 ER8B70830 8LBN0LI

Luminous Intensity Polar Plot





TEST NUMBER: P250819

CATALOG NUMBER: LD8B70D010 ER8B70830 8LBN0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	99	101	99	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	91		94	92	89		92	90	88	87
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		89	86	84	83
5	98	91	86	83	96	90	86	82	88	85	82		87	84	81		85	83	80	79
6	94	87	82	79	93	86	82	78	85	81	78		83	80	77		82	79	77	76
7	91	83	78	75	90	83	78	75	81	77	74		80	77	74		79	76	74	72
8	88	80	75	72	86	79	75	71	78	74	71		77	74	71		76	73	71	70
9	85	77	72	69	84	76	72	69	75	71	68		75	71	68		74	70	68	67
10	82	74	69	66	81	73	69	66	73	69	66		72	68	66		71	68	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1042736
5°	724233
10°	381108
15°	241129
20°	179195
25°	140880
30°	101429
35°	43528
40°	15168
45°	5817
50°	1348
55°	505
60°	0
65°	686
70°	207
75°	560
80°	835
85°	0



TEST NUMBER: P250819

CATALOG NUMBER: LD8B70D010 ER8B70830 8LBN0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1875.7	27.2
10°-20°	2179.4	31.6
20°-30°	1881.0	27.3
30°-40°	816.0	11.8
40°-50°	127.9	1.9
50°-60°	9.2	0.1
60°-70°	5.0	0.1
70°-80°	5.2	0.1
80°-90°	2.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5936.1	86.0
0°-40°	6752.1	97.8
0°-60°	6889.2	99.8
0°-90°	6902.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6902.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	33815	
5°	23397	###
15°	7553	2179
25°	4141	1881
35°	1156	816
45°	133	128
55°	9	9
65°	9	5
75°	5	5
85°	0	3
90°	0	



TEST NUMBER: P250819

CATALOG NUMBER: LD8B70D010 ER8B70830 8LBN0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	33815.2
2.5°	30536.0
5°	23397.0
7.5°	16686.4
10°	12171.3
12.5°	9339.1
15°	7553.2
17.5°	6352.5
20°	5460.7
22.5°	4700.0
25°	4140.6
27.5°	3550.7
30°	2848.6
32.5°	1980.2
35°	1156.3
37.5°	646.0
40°	376.8
42.5°	234.1
45°	133.4
47.5°	107.7
50°	28.1
52.5°	14.0
55°	9.4
57.5°	4.7
60°	0.0
62.5°	2.3
65°	9.4
67.5°	7.0
70°	2.3
72.5°	11.7
75°	4.7
77.5°	0.0
80°	4.7
82.5°	2.3
85°	0.0
87.5°	4.7
90°	0.0

(END OF REPORT)