

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246293

Luminaire Tested: **LD8B50D010 ER8B50935 8LBW0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246293
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-47)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B50D010 ER8B50935 8LBW0B
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 3500 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2988.0 lumens
Efficiency: N/A
Efficacy: 56.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.02
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246293

CATALOG NUMBER: LD8B50D010 ER8B50935 8LBW0B

Luminous Intensity Polar Plot





TEST NUMBER: P246293

CATALOG NUMBER: LD8B50D010 ER8B50935 8LBW0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	106	111	108	106	104	104	102	101		101	99	98		97	96	95	93
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92	90	88	86
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86	84	81	80
4	96	88	83	78	94	87	82	78	85	80	77		83	79	76		81	78	75	74
5	91	82	76	72	89	81	76	71	80	75	71		78	74	70		76	73	70	68
6	86	77	71	66	85	76	70	66	74	69	65		73	68	65		72	68	65	63
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67	63	60	58
8	77	67	61	57	76	67	61	57	66	60	56		65	60	56		64	59	56	54
9	73	63	57	53	72	63	57	53	62	56	52		61	56	52		60	55	52	51
10	70	59	53	49	68	59	53	49	58	53	49		57	52	49		57	52	49	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	84257
5°	82137
10°	79952
15°	78463
20°	76420
25°	73713
30°	67635
35°	51859
40°	24672
45°	9393
50°	4586
55°	1876
60°	469
65°	109
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P246293

CATALOG NUMBER: LD8B50D010 ER8B50935 8LBW0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	250.2	8.4
10°-20°	691.6	23.1
20°-30°	987.6	33.1
30°-40°	818.5	27.4
40°-50°	201.8	6.8
50°-60°	36.3	1.2
60°-70°	2.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1929.4	64.6
0°-40°	2747.9	92.0
0°-60°	2986.0	99.9
0°-90°	2988.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2988.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2732	
5°	2654	250
15°	2458	692
25°	2166	988
35°	1378	818
45°	215	202
55°	35	36
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246293

CATALOG NUMBER: LD8B50D010 ER8B50935 8LBW0B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2732.4
2.5°	2709.6
5°	2653.5
7.5°	2598.9
10°	2553.4
12.5°	2509.4
15°	2457.8
17.5°	2397.1
20°	2328.8
22.5°	2251.5
25°	2166.5
27.5°	2051.2
30°	1899.5
32.5°	1685.6
35°	1377.6
37.5°	995.3
40°	612.9
42.5°	356.5
45°	215.4
47.5°	142.6
50°	95.6
52.5°	62.2
55°	34.9
57.5°	16.7
60°	7.6
62.5°	3.0
65°	1.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)