

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250845

Luminaire Tested: **LD8B70D010 ER8B70835 8LBMOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250845
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-11)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B70D010 ER8B70835 8LBM0LI
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
80 CRI 3500 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7809.9 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 0.63 / 0.63 / 0.72
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250845

CATALOG NUMBER: LD8B70D010 ER8B70835 8LBM0LI

Luminous Intensity Polar Plot





TEST NUMBER: P250845

CATALOG NUMBER: LD8B70D010 ER8B70835 8LBM0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	73	80	75	72		79	75	72		77	74	71	70
7	86	78	72	69	85	77	72	68	76	71	68		75	71	68		74	70	67	66
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	60	59
10	76	67	62	58	75	67	61	58	66	61	58		65	61	58		64	60	58	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	420126
5°	402069
10°	357946
15°	287556
20°	225221
25°	181845
30°	140910
35°	80257
40°	30271
45°	13057
50°	5253
55°	1962
60°	1048
65°	708
70°	442
75°	286
80°	0
85°	0



TEST NUMBER: P250845

CATALOG NUMBER: LD8B70D010 ER8B70835 8LBM0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1192.2	15.3
10°-20°	2501.3	32.0
20°-30°	2447.6	31.3
30°-40°	1354.2	17.3
40°-50°	262.1	3.4
50°-60°	40.2	0.5
60°-70°	9.9	0.1
70°-80°	2.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6141.1	78.6
0°-40°	7495.2	96.0
0°-60°	7797.5	99.8
0°-90°	7809.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7809.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13624	
5°	12989	###
15°	9008	2501
25°	5345	2448
35°	2132	1354
45°	299	262
55°	36	40
65°	10	10
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P250845

CATALOG NUMBER: LD8B70D010 ER8B70835 8LBM0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	13624.4
2.5°	13437.0
5°	12989.2
7.5°	12361.3
10°	11431.6
12.5°	10256.0
15°	9007.5
17.5°	7836.8
20°	6863.3
22.5°	6057.7
25°	5344.6
27.5°	4672.9
30°	3957.4
32.5°	3117.7
35°	2132.0
37.5°	1282.6
40°	752.0
42.5°	469.7
45°	299.4
47.5°	187.4
50°	109.5
52.5°	60.8
55°	36.5
57.5°	21.9
60°	17.0
62.5°	12.2
65°	9.7
67.5°	7.3
70°	4.9
72.5°	2.4
75°	2.4
77.5°	2.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)