

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244727

Luminaire Tested: **LD8B50D010 ER8B509727 8LBW0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244727  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B50D010 ER8B509727 8LBW0WMH  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 2700 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3729.0 lumens  
Efficiency: N/A  
Efficacy: 70.4 lumens/watt  
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 53  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244727

CATALOG NUMBER: LD8B50D010 ER8B509727 8LBW0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P244727

CATALOG NUMBER: LD8B50D010 ER8B509727 8LBW0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P244727

CATALOG NUMBER: LD8B50D010 ER8B509727 8LBW0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	248.1	6.7
10°-20°	690.3	18.5
20°-30°	1028.2	27.6
30°-40°	954.9	25.6
40°-50°	451.0	12.1
50°-60°	242.3	6.5
60°-70°	97.3	2.6
70°-80°	15.3	0.4
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1966.7	52.7
0°-40°	2921.6	78.3
0°-60°	3614.9	96.9
0°-90°	3729.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3729.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2702	
5°	2638	248
15°	2444	690
25°	2250	1028
35°	1587	955
45°	550	451
55°	266	242
65°	97	97
75°	12	15
85°	1	2
90°	0	



TEST NUMBER: P244727

CATALOG NUMBER: LD8B50D010 ER8B509727 8LBW0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2702.4
2.5°	2683.8
5°	2638.0
7.5°	2579.8
10°	2525.2
12.5°	2480.6
15°	2443.5
17.5°	2405.1
20°	2362.9
22.5°	2314.6
25°	2250.2
27.5°	2159.7
30°	2034.6
32.5°	1851.2
35°	1587.3
37.5°	1250.2
40°	926.8
42.5°	690.2
45°	550.2
47.5°	459.7
50°	387.8
52.5°	323.4
55°	266.4
57.5°	216.8
60°	175.9
62.5°	137.5
65°	96.6
67.5°	57.0
70°	33.5
72.5°	19.8
75°	12.4
77.5°	7.4
80°	3.7
82.5°	2.5
85°	1.2
87.5°	0.0
90°	0.0

(END OF REPORT)