

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251181

Luminaire Tested: **LD8B70D010 ER8B70840 8LBS0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251181
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B70D010 ER8B70840 8LBS0WH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 4000 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8353.9 lumens
Efficiency: N/A
Efficacy: 110.1 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251181

CATALOG NUMBER: LD8B70D010 ER8B70840 8LBS0WH

Luminous Intensity Polar Plot





TEST NUMBER: P251181

CATALOG NUMBER: LD8B70D010 ER8B70840 8LBS0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60
6	80	70	63	57	79	69	62	57	67	61	57	66	60	56	64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145911
5°	146469
10°	148312
15°	151212
20°	153372
25°	154003
30°	149285
35°	136257
40°	117868
45°	92787
50°	59851
55°	29375
60°	12076
65°	5290
70°	1524
75°	572
80°	426
85°	0



TEST NUMBER: P251181

CATALOG NUMBER: LD8B70D010 ER8B70840 8LBS0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	451.9	5.4
10°-20°	1338.6	16.0
20°-30°	2072.5	24.8
30°-40°	2245.2	26.9
40°-50°	1615.6	19.3
50°-60°	540.5	6.5
60°-70°	81.7	1.0
70°-80°	7.0	0.1
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3863.0	46.2
0°-40°	6108.1	73.1
0°-60°	8264.3	98.9
0°-90°	8353.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8353.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4732	
5°	4732	452
15°	4737	1339
25°	4526	2072
35°	3620	2245
45°	2128	1616
55°	546	541
65°	72	82
75°	5	7
85°	0	1
90°	0	



TEST NUMBER: P251181

CATALOG NUMBER: LD8B70D010 ER8B70840 8LBS0WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4731.8
2.5°	4731.8
5°	4731.8
7.5°	4734.2
10°	4736.6
12.5°	4741.5
15°	4736.6
17.5°	4717.3
20°	4673.8
22.5°	4608.5
25°	4526.3
27.5°	4395.7
30°	4192.6
32.5°	3926.7
35°	3619.6
37.5°	3288.3
40°	2928.1
42.5°	2541.2
45°	2127.7
47.5°	1680.4
50°	1247.6
52.5°	855.9
55°	546.4
57.5°	326.4
60°	195.8
62.5°	118.5
65°	72.5
67.5°	36.3
70°	16.9
72.5°	7.3
75°	4.8
77.5°	4.8
80°	2.4
82.5°	2.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)