

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244445

Luminaire Tested: **LD8B50D010 ER8B509730 8LBM0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244445
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27951)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B50D010 ER8B509730 8LBM0H
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3997.0 lumens
Efficiency: N/A
Efficacy: 75.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244445

CATALOG NUMBER: LD8B50D010 ER8B509730 8LBM0H

Luminous Intensity Polar Plot






TEST NUMBER: P244445

CATALOG NUMBER: LD8B50D010 ER8B509730 8LBM0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86	83	80	79
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80	77	74	73
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75	72	69	67
6	85	76	70	65	84	75	69	65	74	68	64		72	68	64		71	67	64	62
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67	62	59	58
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63	58	55	54
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59	55	51	50
10	69	59	53	49	68	58	53	49	58	52	48		57	52	48		56	51	48	47

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244445

CATALOG NUMBER: LD8B50D010 ER8B509730 8LBM0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	368.9	9.2
10°-20°	928.6	23.2
20°-30°	1239.0	31.0
30°-40°	955.0	23.9
40°-50°	356.1	8.9
50°-60°	116.4	2.9
60°-70°	26.9	0.7
70°-80°	5.4	0.1
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2536.4	63.5
0°-40°	3491.4	87.4
0°-60°	3964.0	99.2
0°-90°	3997.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3997.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4188	
5°	3995	369
15°	3303	929
25°	2727	1239
35°	1554	955
45°	433	356
55°	122	116
65°	24	27
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P244445

CATALOG NUMBER: LD8B50D010 ER8B509730 8LBM0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	4188.3
1°	4170.2
2°	4139.6
3°	4100.5
4°	4052.7
5°	3995.4
6°	3930.5
7°	3856.0
8°	3776.7
9°	3694.6
10°	3619.2
11°	3546.6
12°	3478.8
13°	3416.7
14°	3359.4
15°	3303.1
16°	3245.8
17°	3190.4
18°	3133.1
19°	3076.8
20°	3022.4
21°	2966.0
22°	2911.6
23°	2854.3
24°	2794.1
25°	2727.3
26°	2653.8
27°	2572.6
28°	2482.8
29°	2382.6
30°	2272.7
32.5°	1950.9
35°	1553.7
37.5°	1150.7
40°	814.6
42.5°	583.5
45°	432.6
47.5°	325.6
50°	240.6
52.5°	171.9
55°	122.2
57.5°	84.0
60°	55.4
62.5°	36.3
65°	23.9



TEST NUMBER: P244445

CATALOG NUMBER: LD8B50D010 ER8B509730 8LBM0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	16.2
70°	10.5
72.5°	6.7
75°	4.8
77.5°	2.9
80°	1.9
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0

(END OF REPORT)