

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246605

Luminaire Tested: **LD8B50D010 ER8B509730 8LBW0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246605
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-48)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B50D010 ER8B509730 8LBW0MW
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4134.0 lumens
Efficiency: N/A
Efficacy: 78.0 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246605

CATALOG NUMBER: LD8B50D010 ER8B509730 8LBW0MW

Luminous Intensity Polar Plot





TEST NUMBER: P246605

CATALOG NUMBER: LD8B50D010 ER8B509730 8LBW0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	86	83	80	78
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62
5	84	73	66	60	82	72	65	60	70	64	59	68	63	59	67	62	58	56
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47
8	69	58	50	45	68	57	50	45	56	50	45	55	49	45	54	48	45	43
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	45	41	40
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P246605

CATALOG NUMBER: LD8B50D010 ER8B509730 8LBW0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.4	6.1
10°-20°	695.1	16.8
20°-30°	1019.4	24.7
30°-40°	931.8	22.5
40°-50°	461.3	11.2
50°-60°	341.1	8.3
60°-70°	262.2	6.3
70°-80°	136.7	3.3
80°-90°	34.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1966.8	47.6
0°-40°	2898.6	70.1
0°-60°	3701.0	89.5
0°-90°	4134.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4134.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2739	
5°	2683	252
15°	2461	695
25°	2232	1019
35°	1546	932
45°	560	461
55°	378	341
65°	268	262
75°	127	137
85°	29	34
90°	0	



TEST NUMBER: P246605

CATALOG NUMBER: LD8B50D010 ER8B509730 8LBW0MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2739.1
2.5°	2724.6
5°	2682.7
7.5°	2626.3
10°	2568.6
12.5°	2512.2
15°	2461.1
17.5°	2412.6
20°	2360.1
22.5°	2301.1
25°	2231.6
27.5°	2135.9
30°	2002.2
32.5°	1814.7
35°	1545.9
37.5°	1212.8
40°	895.5
42.5°	677.9
45°	559.9
47.5°	495.6
50°	448.4
52.5°	410.4
55°	377.6
57.5°	350.1
60°	326.5
62.5°	301.6
65°	267.5
67.5°	230.8
70°	194.1
72.5°	160.0
75°	127.2
77.5°	98.3
80°	72.1
82.5°	49.8
85°	28.8
87.5°	10.5
90°	0.0

(END OF REPORT)