

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250945

Luminaire Tested: **LD8B70D010 ER8B70850 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250945
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27944)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B70D010 ER8B70850 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 5000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6907.0 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.79
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250945

CATALOG NUMBER: LD8B70D010 ER8B70850 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P250945

CATALOG NUMBER: LD8B70D010 ER8B70850 8LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | | 106 | 106 | 106 | | 102 | 102 | 102 | 100 |
| 1 | 114 | 111 | 109 | 106 | 111 | 109 | 107 | 105 | 105 | 103 | 101 | | 101 | 100 | 98 | | 98 | 97 | 96 | 94 |
| 2 | 108 | 104 | 100 | 96 | 106 | 102 | 98 | 95 | 99 | 96 | 93 | | 96 | 93 | 91 | | 93 | 91 | 89 | 88 |
| 3 | 103 | 97 | 92 | 88 | 101 | 95 | 91 | 87 | 93 | 89 | 86 | | 90 | 87 | 85 | | 88 | 86 | 83 | 82 |
| 4 | 98 | 91 | 85 | 81 | 96 | 90 | 85 | 81 | 87 | 83 | 80 | | 85 | 82 | 79 | | 84 | 80 | 78 | 76 |
| 5 | 93 | 85 | 79 | 75 | 92 | 84 | 79 | 75 | 82 | 78 | 74 | | 81 | 77 | 74 | | 79 | 76 | 73 | 72 |
| 6 | 89 | 80 | 74 | 70 | 87 | 79 | 74 | 70 | 78 | 73 | 69 | | 76 | 72 | 69 | | 75 | 71 | 69 | 67 |
| 7 | 85 | 76 | 70 | 66 | 83 | 75 | 69 | 65 | 74 | 69 | 65 | | 72 | 68 | 65 | | 71 | 67 | 64 | 63 |
| 8 | 81 | 71 | 66 | 62 | 79 | 71 | 65 | 61 | 70 | 65 | 61 | | 69 | 64 | 61 | | 68 | 64 | 61 | 59 |
| 9 | 77 | 68 | 62 | 58 | 76 | 67 | 62 | 58 | 66 | 61 | 58 | | 65 | 61 | 58 | | 64 | 60 | 57 | 56 |
| 10 | 74 | 64 | 59 | 55 | 73 | 64 | 58 | 55 | 63 | 58 | 55 | | 62 | 58 | 54 | | 61 | 57 | 54 | 53 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 325126 |
| 5° | 303264 |
| 10° | 261411 |
| 15° | 226233 |
| 20° | 196803 |
| 25° | 169130 |
| 30° | 132891 |
| 35° | 77536 |
| 40° | 35774 |
| 45° | 18512 |
| 50° | 9288 |
| 55° | 4516 |
| 60° | 2300 |
| 65° | 1364 |
| 70° | 631 |
| 75° | 560 |
| 80° | 408 |
| 85° | 0 |



TEST NUMBER: P250945

CATALOG NUMBER: LD8B70D010 ER8B70850 8LBN0H

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 886.6 | 12.8 |
| 10°-20° | 1981.4 | 28.7 |
| 20°-30° | 2252.8 | 32.6 |
| 30°-40° | 1323.0 | 19.2 |
| 40°-50° | 355.0 | 5.1 |
| 50°-60° | 84.3 | 1.2 |
| 60°-70° | 19.2 | 0.3 |
| 70°-80° | 4.3 | 0.1 |
| 80°-90° | 0.3 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 5120.9 | 74.1 |
| 0°-40° | 6443.9 | 93.3 |
| 0°-60° | 6883.2 | 99.7 |
| 0°-90° | 6907.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 6907.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 10544 | |
| 5° | 9797 | 887 |
| 15° | 7087 | 1981 |
| 25° | 4971 | 2253 |
| 35° | 2060 | 1323 |
| 45° | 424 | 355 |
| 55° | 84 | 84 |
| 65° | 19 | 19 |
| 75° | 5 | 4 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P250945

CATALOG NUMBER: LD8B70D010 ER8B70850 8LBN0H

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|---------|
| 0° | 10543.6 |
| 1° | 10485.3 |
| 2° | 10378.0 |
| 3° | 10226.4 |
| 4° | 10030.4 |
| 5° | 9797.2 |
| 6° | 9533.6 |
| 7° | 9235.0 |
| 8° | 8936.4 |
| 9° | 8635.5 |
| 10° | 8348.6 |
| 11° | 8068.7 |
| 12° | 7805.1 |
| 13° | 7560.1 |
| 14° | 7315.2 |
| 15° | 7086.6 |
| 16° | 6862.7 |
| 17° | 6641.1 |
| 18° | 6426.5 |
| 19° | 6209.5 |
| 20° | 5997.3 |
| 21° | 5785.0 |
| 22° | 5582.0 |
| 23° | 5381.4 |
| 24° | 5176.2 |
| 25° | 4970.9 |
| 26° | 4758.6 |
| 27° | 4527.7 |
| 28° | 4285.1 |
| 29° | 4019.2 |
| 30° | 3732.2 |
| 32.5° | 2927.5 |
| 35° | 2059.7 |
| 37.5° | 1357.6 |
| 40° | 888.7 |
| 42.5° | 613.5 |
| 45° | 424.5 |
| 47.5° | 291.6 |
| 50° | 193.6 |
| 52.5° | 126.0 |
| 55° | 84.0 |
| 57.5° | 56.0 |
| 60° | 37.3 |
| 62.5° | 25.7 |
| 65° | 18.7 |



TEST NUMBER: P250945

CATALOG NUMBER: LD8B70D010 ER8B70850 8LBN0H

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|------|
| 67.5° | 11.7 |
| 70° | 7.0 |
| 72.5° | 4.7 |
| 75° | 4.7 |
| 77.5° | 2.3 |
| 80° | 2.3 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)