

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251017

Luminaire Tested: **LD8B70D010 ER8B70850 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251017
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B70D010 ER8B70850 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 5000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7418.0 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251017

CATALOG NUMBER: LD8B70D010 ER8B70850 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P251017

CATALOG NUMBER: LD8B70D010 ER8B70850 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	165773
5°	162438
10°	157293
15°	155173
20°	154248
25°	152299
30°	144111
35°	118862
40°	74216
45°	47726
50°	37011
55°	28488
60°	21585
65°	14031
70°	6005
75°	2931
80°	1314
85°	885



TEST NUMBER: P251017

CATALOG NUMBER: LD8B70D010 ER8B70850 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	493.6	6.7
10°-20°	1373.2	18.5
20°-30°	2045.4	27.6
30°-40°	1899.5	25.6
40°-50°	897.2	12.1
50°-60°	482.0	6.5
60°-70°	193.6	2.6
70°-80°	30.4	0.4
80°-90°	3.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3912.2	52.7
0°-40°	5811.8	78.3
0°-60°	7191.0	96.9
0°-90°	7418.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7418.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5376	
5°	5248	494
15°	4861	1373
25°	4476	2045
35°	3158	1900
45°	1094	897
55°	530	482
65°	192	194
75°	25	30
85°	2	3
90°	0	



TEST NUMBER: P251017

CATALOG NUMBER: LD8B70D010 ER8B70850 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5375.9
2.5°	5338.9
5°	5247.7
7.5°	5131.8
10°	5023.4
12.5°	4934.7
15°	4860.7
17.5°	4784.3
20°	4700.5
22.5°	4604.4
25°	4476.2
27.5°	4296.3
30°	4047.3
32.5°	3682.5
35°	3157.5
37.5°	2487.0
40°	1843.7
42.5°	1372.9
45°	1094.4
47.5°	914.5
50°	771.5
52.5°	643.3
55°	529.9
57.5°	431.4
60°	350.0
62.5°	273.6
65°	192.3
67.5°	113.4
70°	66.6
72.5°	39.4
75°	24.6
77.5°	14.8
80°	7.4
82.5°	4.9
85°	2.5
87.5°	0.0
90°	0.0

(END OF REPORT)