

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250837

Luminaire Tested: **LD8B70D010 ER8B70927 8LBNOLI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250837  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-10)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B70D010 ER8B70927 8LBN0LI  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 2700 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5621.6 lumens  
Efficiency: N/A  
Efficacy: 74.1 lumens/watt  
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.32  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 75.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250837

CATALOG NUMBER: LD8B70D010 ER8B70927 8LBN0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P250837

CATALOG NUMBER: LD8B70D010 ER8B70927 8LBN0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	99	101	99	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	91		94	92	89		92	90	88	87
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		89	86	84	83
5	98	91	86	83	96	90	86	82	88	85	82		87	84	81		85	83	80	79
6	94	87	82	79	93	86	82	78	85	81	78		83	80	77		82	79	77	76
7	91	83	78	75	90	83	78	75	81	77	74		80	77	74		79	76	74	72
8	88	80	75	72	86	79	75	71	78	74	71		77	74	71		76	73	71	70
9	85	77	72	69	84	76	72	69	75	71	68		75	71	68		74	70	68	67
10	82	74	69	66	81	73	69	66	73	69	66		72	68	66		71	68	65	64

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P250837

CATALOG NUMBER: LD8B70D010 ER8B70927 8LBN0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1527.8	27.2
10°-20°	1775.1	31.6
20°-30°	1532.0	27.3
30°-40°	664.6	11.8
40°-50°	104.2	1.9
50°-60°	7.5	0.1
60°-70°	4.0	0.1
70°-80°	4.3	0.1
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4834.9	86.0
0°-40°	5499.5	97.8
0°-60°	5611.3	99.8
0°-90°	5621.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5621.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	27542	
5°	19057	###
15°	6152	1775
25°	3372	1532
35°	942	665
45°	109	104
55°	8	8
65°	8	4
75°	4	4
85°	0	2
90°	0	



TEST NUMBER: P250837

CATALOG NUMBER: LD8B70D010 ER8B70927 8LBN0LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	27542.2
2.5°	24871.3
5°	19056.7
7.5°	13590.9
10°	9913.5
12.5°	7606.7
15°	6152.1
17.5°	5174.1
20°	4447.7
22.5°	3828.2
25°	3372.5
27.5°	2892.0
30°	2320.1
32.5°	1612.8
35°	941.7
37.5°	526.2
40°	306.9
42.5°	190.7
45°	108.7
47.5°	87.8
50°	22.8
52.5°	11.5
55°	7.6
57.5°	3.8
60°	0.0
62.5°	1.9
65°	7.6
67.5°	5.7
70°	1.9
72.5°	9.6
75°	3.8
77.5°	0.0
80°	3.8
82.5°	1.9
85°	0.0
87.5°	3.8
90°	0.0

(END OF REPORT)