

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250988

Luminaire Tested: **LD8B60D010 ER8B60835 8LBS0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250988
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B60835 8LBS0H
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3500 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6837.0 lumens
Efficiency: N/A
Efficacy: 114.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250988

CATALOG NUMBER: LD8B60D010 ER8B60835 8LBS0H

Luminous Intensity Polar Plot





TEST NUMBER: P250988

CATALOG NUMBER: LD8B60D010 ER8B60835 8LBSOH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81	78	75	73
4	91	82	75	70	89	81	75	70	79	73	69		76	72	68		74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62		70	65	61		69	64	60	59
6	80	69	61	56	78	68	61	56	66	60	56		65	59	55		63	58	55	53
7	75	63	56	51	73	63	56	51	61	55	50		60	54	50		59	54	50	48
8	70	58	51	46	68	58	51	46	57	50	46		55	50	46		54	49	45	44
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	122349
5°	121944
10°	121018
15°	120166
20°	119353
25°	117781
30°	114141
35°	107696
40°	97873
45°	80537
50°	53677
55°	27967
60°	13179
65°	6917
70°	3453
75°	2407
80°	1794
85°	1415



TEST NUMBER: P250988

CATALOG NUMBER: LD8B60D010 ER8B60835 8LBSOH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	373.7	5.5
10°-20°	1062.4	15.5
20°-30°	1589.3	23.2
30°-40°	1777.6	26.0
40°-50°	1394.6	20.4
50°-60°	508.9	7.4
60°-70°	103.7	1.5
70°-80°	22.3	0.3
80°-90°	4.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3025.3	44.2
0°-40°	4802.9	70.2
0°-60°	6706.4	98.1
0°-90°	6837.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6837.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3968	
5°	3940	374
15°	3764	1062
25°	3462	1589
35°	2861	1778
45°	1847	1395
55°	520	509
65°	95	104
75°	20	22
85°	4	5
90°	0	



TEST NUMBER: P250988

CATALOG NUMBER: LD8B60D010 ER8B60835 8LBS0H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3967.7
2.5°	3961.6
5°	3939.5
7.5°	3907.2
10°	3864.9
12.5°	3816.5
15°	3764.1
17.5°	3705.6
20°	3637.1
22.5°	3556.4
25°	3461.7
27.5°	3344.7
30°	3205.6
32.5°	3042.3
35°	2860.9
37.5°	2657.2
40°	2431.4
42.5°	2163.3
45°	1846.8
47.5°	1489.9
50°	1118.9
52.5°	784.3
55°	520.2
57.5°	332.7
60°	213.7
62.5°	141.1
65°	94.8
67.5°	60.5
70°	38.3
72.5°	26.2
75°	20.2
77.5°	14.1
80°	10.1
82.5°	6.0
85°	4.0
87.5°	2.0
90°	0.0

(END OF REPORT)