

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251084

Luminaire Tested: **LD8B60D010 ER8B60835 8LBS0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P251084  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B60D010 ER8B60835 8LBS0WMH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 3500 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6704.0 lumens  
Efficiency: N/A  
Efficacy: 112.7 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 59.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P251084

CATALOG NUMBER: LD8B60D010 ER8B60835 8LBS0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P251084

CATALOG NUMBER: LD8B60D010 ER8B60835 8LBS0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55	64	58	54	63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	117212
5°	116849
10°	115798
15°	114652
20°	113416
25°	111626
30°	108561
35°	103616
40°	96026
45°	81078
50°	55624
55°	30682
60°	15418
65°	8683
70°	4724
75°	3360
80°	2149
85°	1415



TEST NUMBER: P251084

CATALOG NUMBER: LD8B60D010 ER8B60835 8LBS0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	357.8	5.3
10°-20°	1012.8	15.1
20°-30°	1507.9	22.5
30°-40°	1712.9	25.6
40°-50°	1400.2	20.9
50°-60°	548.7	8.2
60°-70°	127.9	1.9
70°-80°	30.8	0.5
80°-90°	4.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2878.6	42.9
0°-40°	4591.6	68.5
0°-60°	6540.4	97.6
0°-90°	6704.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6704.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3801	
5°	3775	358
15°	3591	1013
25°	3281	1508
35°	2752	1713
45°	1859	1400
55°	571	549
65°	119	128
75°	28	31
85°	4	5
90°	0	



TEST NUMBER: P251084

CATALOG NUMBER: LD8B60D010 ER8B60835 8LBS0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3801.1
2.5°	3795.0
5°	3774.9
7.5°	3740.6
10°	3698.2
12.5°	3645.8
15°	3591.4
17.5°	3526.8
20°	3456.2
22.5°	3373.6
25°	3280.8
27.5°	3171.9
30°	3048.9
32.5°	2909.8
35°	2752.5
37.5°	2579.1
40°	2385.5
42.5°	2151.6
45°	1859.2
47.5°	1516.4
50°	1159.5
52.5°	832.8
55°	570.7
57.5°	373.0
60°	250.0
62.5°	171.4
65°	119.0
67.5°	78.6
70°	52.4
72.5°	36.3
75°	28.2
77.5°	20.2
80°	12.1
82.5°	6.0
85°	4.0
87.5°	2.0
90°	0.0

(END OF REPORT)