

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251233

Luminaire Tested: **LD8B70D010 ER8B70935 8LBW0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251233
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B70D010 ER8B70935 8LBW0GPH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 3500 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5749.0 lumens
Efficiency: N/A
Efficacy: 75.7 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251233

CATALOG NUMBER: LD8B70D010 ER8B70935 8LBW0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P251233

CATALOG NUMBER: LD8B70D010 ER8B70935 8LBW0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70
5	88	79	72	67	87	78	72	67	76	71	66	74	70	66	73	69	65	64
6	83	73	66	61	82	72	66	61	71	65	61	69	64	60	68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55	54
8	74	63	56	52	73	63	56	52	61	56	51	60	55	51	59	55	51	49
9	70	59	52	48	69	58	52	48	57	52	48	57	51	47	56	51	47	46
10	66	55	49	44	65	55	49	44	54	48	44	53	48	44	52	47	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	138039
5°	134774
10°	130549
15°	128664
20°	127146
25°	124416
30°	116534
35°	95153
40°	56806
45°	34120
50°	24591
55°	16736
60°	10497
65°	5151
70°	1307
75°	500
80°	373
85°	0



TEST NUMBER: P251233

CATALOG NUMBER: LD8B70D010 ER8B70935 8LBW0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	409.6	7.1
10°-20°	1137.4	19.8
20°-30°	1670.2	29.1
30°-40°	1514.1	26.3
40°-50°	648.1	11.3
50°-60°	286.8	5.0
60°-70°	76.5	1.3
70°-80°	6.0	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3217.2	56.0
0°-40°	4731.3	82.3
0°-60°	5666.3	98.6
0°-90°	5749.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5749.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4476	
5°	4354	410
15°	4030	1137
25°	3657	1670
35°	2528	1514
45°	782	648
55°	311	287
65°	71	76
75°	4	6
85°	0	0
90°	0	



TEST NUMBER: P251233

CATALOG NUMBER: LD8B70D010 ER8B70935 8LBW0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4476.5
2.5°	4441.2
5°	4354.0
7.5°	4254.4
10°	4169.3
12.5°	4098.8
15°	4030.3
17.5°	3957.6
20°	3874.6
22.5°	3777.1
25°	3656.7
27.5°	3494.8
30°	3272.8
32.5°	2961.5
35°	2527.7
37.5°	1959.1
40°	1411.2
42.5°	1019.0
45°	782.4
47.5°	630.9
50°	512.6
52.5°	406.8
55°	311.3
57.5°	232.4
60°	170.2
62.5°	118.3
65°	70.6
67.5°	31.1
70°	14.5
72.5°	8.3
75°	4.2
77.5°	2.1
80°	2.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)