

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251411

Luminaire Tested: **LD8B70D010 ER8B70940 8LBS0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251411
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-17)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B70D010 ER8B70940 8LBS0B
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 4000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6111.0 lumens
Efficiency: N/A
Efficacy: 80.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 75.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251411

CATALOG NUMBER: LD8B70D010 ER8B70940 8LBS0B

Luminous Intensity Polar Plot





TEST NUMBER: P251411

CATALOG NUMBER: LD8B70D010 ER8B70940 8LBS0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | | 106 | 106 | 106 | | 102 | 102 | 102 | 100 |
| 1 | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 102 | 103 | 101 | 99 | | 99 | 97 | 96 | | 96 | 94 | 93 | 91 |
| 2 | 105 | 99 | 94 | 90 | 103 | 98 | 93 | 89 | 94 | 90 | 87 | | 91 | 88 | 85 | | 88 | 86 | 84 | 82 |
| 3 | 98 | 90 | 84 | 79 | 96 | 89 | 83 | 79 | 86 | 81 | 77 | | 84 | 80 | 76 | | 81 | 78 | 75 | 73 |
| 4 | 92 | 82 | 76 | 70 | 90 | 81 | 75 | 70 | 79 | 73 | 69 | | 77 | 72 | 68 | | 75 | 71 | 67 | 66 |
| 5 | 86 | 75 | 68 | 63 | 84 | 74 | 68 | 63 | 72 | 66 | 62 | | 71 | 65 | 61 | | 69 | 64 | 61 | 59 |
| 6 | 80 | 69 | 62 | 56 | 78 | 68 | 61 | 56 | 67 | 60 | 56 | | 65 | 60 | 55 | | 64 | 59 | 55 | 53 |
| 7 | 75 | 63 | 56 | 51 | 73 | 63 | 56 | 51 | 61 | 55 | 51 | | 60 | 54 | 50 | | 59 | 54 | 50 | 48 |
| 8 | 70 | 59 | 51 | 46 | 69 | 58 | 51 | 46 | 57 | 50 | 46 | | 56 | 50 | 46 | | 54 | 49 | 46 | 44 |
| 9 | 66 | 54 | 47 | 42 | 65 | 54 | 47 | 42 | 53 | 46 | 42 | | 52 | 46 | 42 | | 51 | 45 | 42 | 40 |
| 10 | 62 | 50 | 43 | 39 | 61 | 50 | 43 | 39 | 49 | 43 | 39 | | 48 | 42 | 38 | | 47 | 42 | 38 | 37 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 109164 |
| 5° | 109042 |
| 10° | 108471 |
| 15° | 107686 |
| 20° | 106496 |
| 25° | 104811 |
| 30° | 101735 |
| 35° | 96949 |
| 40° | 89794 |
| 45° | 75348 |
| 50° | 49815 |
| 55° | 24590 |
| 60° | 9763 |
| 65° | 3794 |
| 70° | 586 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P251411

CATALOG NUMBER: LD8B70D010 ER8B70940 8LBS0B

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 334.3 | 5.5 |
| 10°-20° | 950.8 | 15.6 |
| 20°-30° | 1415.2 | 23.2 |
| 30°-40° | 1602.9 | 26.2 |
| 40°-50° | 1295.9 | 21.2 |
| 50°-60° | 449.5 | 7.4 |
| 60°-70° | 61.5 | 1.0 |
| 70°-80° | 0.8 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 2700.4 | 44.2 |
| 0°-40° | 4303.3 | 70.4 |
| 0°-60° | 6048.7 | 99.0 |
| 0°-90° | 6111.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 6111.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 3540 | |
| 5° | 3523 | 334 |
| 15° | 3373 | 951 |
| 25° | 3080 | 1415 |
| 35° | 2575 | 1603 |
| 45° | 1728 | 1296 |
| 55° | 457 | 449 |
| 65° | 52 | 61 |
| 75° | 0 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P251411

CATALOG NUMBER: LD8B70D010 ER8B70940 8LBS0B

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 3540.1 |
| 2.5° | 3535.8 |
| 5° | 3522.7 |
| 7.5° | 3496.7 |
| 10° | 3464.2 |
| 12.5° | 3420.9 |
| 15° | 3373.2 |
| 17.5° | 3312.5 |
| 20° | 3245.3 |
| 22.5° | 3167.2 |
| 25° | 3080.5 |
| 27.5° | 2976.4 |
| 30° | 2857.2 |
| 32.5° | 2722.8 |
| 35° | 2575.4 |
| 37.5° | 2412.8 |
| 40° | 2230.7 |
| 42.5° | 2007.4 |
| 45° | 1727.8 |
| 47.5° | 1389.6 |
| 50° | 1038.4 |
| 52.5° | 711.1 |
| 55° | 457.4 |
| 57.5° | 271.0 |
| 60° | 158.3 |
| 62.5° | 93.2 |
| 65° | 52.0 |
| 67.5° | 23.8 |
| 70° | 6.5 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)