

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250848

Luminaire Tested: **LD8B60D010 ER8B60850 8LBMOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250848
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-11)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B60850 8LBM0LI
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
80 CRI 5000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6554.0 lumens
Efficiency: N/A
Efficacy: 110.2 lumens/watt
Spacing Criteria (0/90/45): 0.63 / 0.63 / 0.72
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250848

CATALOG NUMBER: LD8B60D010 ER8B60850 8LBM0LI

Luminous Intensity Polar Plot





TEST NUMBER: P250848

CATALOG NUMBER: LD8B60D010 ER8B60850 8LBM0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	73	80	75	72		79	75	72		77	74	71	70
7	86	78	72	69	85	77	72	68	76	71	68		75	71	68		74	70	67	66
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70	67	64	62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	60	59
10	76	67	62	58	75	67	61	58	66	61	58		65	61	58		64	60	58	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	352564
5°	337409
10°	300382
15°	241311
20°	189003
25°	152602
30°	118246
35°	67349
40°	25404
45°	10955
50°	4409
55°	1645
60°	882
65°	598
70°	370
75°	238
80°	0
85°	0



TEST NUMBER: P250848

CATALOG NUMBER: LD8B60D010 ER8B60850 8LBM0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1000.5	15.3
10°-20°	2099.0	32.0
20°-30°	2054.0	31.3
30°-40°	1136.4	17.3
40°-50°	220.0	3.4
50°-60°	33.7	0.5
60°-70°	8.3	0.1
70°-80°	2.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5153.5	78.6
0°-40°	6289.8	96.0
0°-60°	6543.5	99.8
0°-90°	6554.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6554.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11433	
5°	10900	###
15°	7559	2099
25°	4485	2054
35°	1789	1136
45°	251	220
55°	31	34
65°	8	8
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P250848

CATALOG NUMBER: LD8B60D010 ER8B60850 8LBM0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	11433.4
2.5°	11276.1
5°	10900.3
7.5°	10373.3
10°	9593.2
12.5°	8606.7
15°	7558.9
17.5°	6576.5
20°	5759.6
22.5°	5083.5
25°	4485.1
27.5°	3921.4
30°	3320.9
32.5°	2616.3
35°	1789.1
37.5°	1076.3
40°	631.1
42.5°	394.2
45°	251.2
47.5°	157.3
50°	91.9
52.5°	51.1
55°	30.6
57.5°	18.4
60°	14.3
62.5°	10.2
65°	8.2
67.5°	6.1
70°	4.1
72.5°	2.0
75°	2.0
77.5°	2.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)