

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251226

Luminaire Tested: **LD8B60D010 ER8B60850 8LBW0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251226
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B60850 8LBW0GPH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 5000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5657.0 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251226

CATALOG NUMBER: LD8B60D010 ER8B60850 8LBW0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P251226

CATALOG NUMBER: LD8B60D010 ER8B60850 8LBW0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100		100	98	97		96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89		93	90	87		90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78	74	71	70
5	88	79	72	67	87	78	72	67	76	71	66		74	70	66		73	69	65	64
6	83	73	66	61	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		65	59	56		63	59	55	54
8	74	63	56	52	73	63	56	52	61	56	51		60	55	51		59	55	51	49
9	70	59	52	48	69	58	52	48	57	52	48		57	51	47		56	51	47	46
10	66	55	49	44	65	55	49	44	54	48	44		53	48	44		52	47	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	135828
5°	132617
10°	128461
15°	126605
20°	125112
25°	122426
30°	114668
35°	93632
40°	55897
45°	33575
50°	24197
55°	16467
60°	10330
65°	5064
70°	1289
75°	488
80°	355
85°	0



TEST NUMBER: P251226

CATALOG NUMBER: LD8B60D010 ER8B60850 8LBW0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	403.1	7.1
10°-20°	1119.2	19.8
20°-30°	1643.5	29.1
30°-40°	1489.9	26.3
40°-50°	637.8	11.3
50°-60°	282.2	5.0
60°-70°	75.2	1.3
70°-80°	5.9	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3165.7	56.0
0°-40°	4655.6	82.3
0°-60°	5575.6	98.6
0°-90°	5657.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5657.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4405	
5°	4284	403
15°	3966	1119
25°	3598	1643
35°	2487	1490
45°	770	638
55°	306	282
65°	69	75
75°	4	6
85°	0	0
90°	0	



TEST NUMBER: P251226

CATALOG NUMBER: LD8B60D010 ER8B60850 8LBW0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4404.8
2.5°	4370.1
5°	4284.3
7.5°	4186.3
10°	4102.6
12.5°	4033.2
15°	3965.8
17.5°	3894.3
20°	3812.6
22.5°	3716.6
25°	3598.2
27.5°	3438.9
30°	3220.4
32.5°	2914.1
35°	2487.3
37.5°	1927.8
40°	1388.6
42.5°	1002.7
45°	769.9
47.5°	620.8
50°	504.4
52.5°	400.3
55°	306.3
57.5°	228.7
60°	167.5
62.5°	116.4
65°	69.4
67.5°	30.6
70°	14.3
72.5°	8.2
75°	4.1
77.5°	2.0
80°	2.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)