

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P251112

Luminaire Tested: **LD8B60D010 ER8B60850 8LBW0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P251112
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P200903)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B60D010 ER8B60850 8LBW0WH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 5000 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6523.0 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.11
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 59.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P251112

CATALOG NUMBER: LD8B60D010 ER8B60850 8LBW0WH

Luminous Intensity Polar Plot





TEST NUMBER: P251112

CATALOG NUMBER: LD8B60D010 ER8B60850 8LBW0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64
6	83	73	67	62	82	73	66	62	71	65	61	69	64	61	68	64	60	59
7	78	68	61	57	77	67	61	56	66	60	56	65	60	56	64	59	55	54
8	74	63	57	52	73	63	56	52	62	56	52	61	55	51	59	55	51	50
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46
10	66	55	49	45	65	55	49	44	54	48	44	53	48	44	52	48	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	131770
5°	135808
10°	144755
15°	149220
20°	149211
25°	144653
30°	129466
35°	103119
40°	75343
45°	48123
50°	26025
55°	13381
60°	5816
65°	1197
70°	820
75°	0
80°	266
85°	0



TEST NUMBER: P251112

CATALOG NUMBER: LD8B60D010 ER8B60850 8LBW0WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	427.0	6.5
10°-20°	1314.0	20.1
20°-30°	1927.8	29.6
30°-40°	1703.0	26.1
40°-50°	872.3	13.4
50°-60°	243.9	3.7
60°-70°	31.2	0.5
70°-80°	3.2	0.0
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3668.8	56.2
0°-40°	5371.8	82.4
0°-60°	6488.0	99.5
0°-90°	6523.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6523.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4273	
5°	4387	427
15°	4674	1314
25°	4252	1928
35°	2739	1703
45°	1104	872
55°	249	244
65°	16	31
75°	0	3
85°	0	1
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P251112

CATALOG NUMBER: LD8B60D010 ER8B60850 8LBW0WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4273.2
2.5°	4289.6
5°	4387.4
7.5°	4521.5
10°	4623.0
12.5°	4672.5
15°	4674.2
17.5°	4627.2
20°	4547.0
22.5°	4420.2
25°	4251.5
27.5°	3999.7
30°	3636.0
32.5°	3204.9
35°	2739.3
37.5°	2285.5
40°	1871.7
42.5°	1481.1
45°	1103.5
47.5°	787.6
50°	542.5
52.5°	379.1
55°	248.9
57.5°	158.1
60°	94.3
62.5°	48.9
65°	16.4
67.5°	10.7
70°	9.1
72.5°	5.3
75°	0.0
77.5°	1.5
80°	1.5
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P251112

CATALOG NUMBER: LD8B60D010 ER8B60850 8LBW0WH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)